



Main

Device application	Distribution
Range	Acti 9
Product name	Acti 9 K60
Product or component type	Miniature circuit-breaker
Device short name	K60N
Poles description	1P
Number of protected poles	1
[In] rated current	10 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn 230 V AC 50/60 Hz EN/IEC 60898-1
Utilisation category	Category A IEC 60947-2
Suitability for isolation	Yes EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product certifications	OVE VDE

Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation class	3 EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 kVEN/IEC 60898-1
Contact position indicator	No
Control type	Toggle
Local signalling	Without
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Downside biconnect
9 mm pitches	2
Maksimalna visina	81 mm
Maksimalna širina	18 mm
Maksimalna dubina	70 mm
Neto težina	0,12 kg
Colour	Bijelo
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Connections - terminals	Tunnel type terminals downstream) 0,5...35 mm ² rigid Tunnel type terminals upstream) 0,5...35 mm ² rigid Tunnel type terminals downstream) 0,5...25 mm ² flexible Tunnel type terminals upstream) 0,5...25 mm ² flexible
Wire stripping length	14 mm top or bottom
Tightening torque	3,5 N.m top or bottom
Earth-leakage protection	Without

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20 IEC 60529
Pollution degree	2 IEC 60898-1 2 EN 60898-1
Overvoltage category	II
Tropicalisation	2 IEC 60068-1
Relative humidity	95 % 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C

Broj pakirnih jedinica

Paket 1 Težina	106 g
Paket 2 Težina	1,322 kg
Paket 3 Težina	16,577 kg

Offer Sustainability

Status održive ponude	Proizvod Green Premium
Uredba REACH	Izjava REACH
Direktiva EU RoHS	Sukladno Izjava EU RoHS
Bez žive	Da
Informacije o RoHS izuzeću	Da
Propis RoHS za Kinu	Izjava RoHS Za Kinu
Izjava o očuvanju okoliša	Ekološki Profil Proizvoda
WEEE	Proizvod se na tržištima EU mora odlagati u skladu sa specifičnim propisima o prikupljanju otpada; nikako se ne smije odlagati s komunalnim otpadom.

Contractual warranty

Jamstvo	18 months
---------	-----------