



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1FG
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F225 LC1F185
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	240 V AC 50 Hz
Average resistance	20.1 Ohm at 20 °C
Inductance of closed circuit	3.09 H
Operating time	20...35 ms closing 7...15 ms opening
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 55 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.35...0.55 Uc 50/60 Hz (at 55 °C) Operational: 0.85...1.1 Uc 50/60 Hz (at 55 °C)
Inrush power in VA	805 VA 50 Hz cos phi 0.3 (at 20 °C)
Hold-in power consumption in VA	55 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	18...24 W at 50 Hz

### Environment

Ambient air temperature for operation	-5...55 °C
Net weight	0.55 kg

### Packing Units

Package 1 Weight	0.522 kg
Package 1 Height	0.700 dm
Package 1 width	0.820 dm
Package 1 Length	1.600 dm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---