



Main

Range of product	Resi9
Product or component type	Base
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 Resi9 MP
[In] rated current	63 A
Nb of horizontal rows	2
Nb of 18 mm modules per row	12
Number of terminal blocks	1 earth (screw) with 16 outgoers 1 neutral (screw) with 16 outgoers
Terminal block function	Earth / neutral

Complementary

Enclosure mounting	Flush
9 mm pitches	4
Total number of 18 mm modules	24
Cable entry	Pre-cutted holes
Distribution block outgoers	2 x 16 mm ² for earth 2 x 16 mm ² for neutral 6 x 6 mm ² for earth 6 x 6 mm ² for neutral 8 x 10 mm ² for earth 8 x 10 mm ² for neutral
Enclosure material	Back part: technoplastic
Width	270 mm wall:
Height	353 mm wall:
Depth	80 Mm wall: 18 Mm outside: 98 mm total:

Environment

Standards	IEC 60695-2-11 EN 50102
Fire resistance	Back part: 650 °C
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	27 cm
Package 1 Length	35.3 cm
Package 1 Weight	814 g
Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	52 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.798 kg
Unit Type of Package 3	P12
Number of Units in Package 3	112
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	104.768 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------