

Product data sheet

Characteristics

GRO

Exclusive - ceiling rose - 150 W - white



Main

Range of product	Exclusive
Product or component type	Ceiling rose
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 10

Complementary

Device mounting	Ceiling
Fixing mode	By screws
Current consumption	6 A
Rated lamp wattage	150 W
Material	Urea (carbamide)
Type of installation	Indoor
Height	88 mm
Length	88 mm
Width	32 mm
Net weight	0.082 kg

Environment

Standards	BS 67 BS EN 61184
IP degree of protection	IP20

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------