



### Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Switch
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	2
Device application	Light control
Provided equipment	Internal power connection
Colour tint	White

### Complementary

Rated current	10 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	10000 cycles
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm <sup>2</sup> rigid cable 0...2.5 mm <sup>2</sup> flexible cable
Material	ASA + PC: mechanism cover
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.039 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EN 60669-1 LV directive EMC directive
Product certifications	14.10.01/5433






## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Petrol Acetone Window-cleaning fluid Alcohol Bleach Liquid soap Oil UV resistant

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.5 cm
Package 1 Length	6.5 cm
Package 1 Weight	36.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.5 cm
Package 2 Width	13.5 cm
Package 2 Length	33.5 cm
Package 2 Weight	428.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.562 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------