

Product data sheet

Characteristics

XVBC21

Base unit + cover for modular tower lights,
plastic, black, Ø70, bottom entry, side cable
entry



Local distributor code: 380607398
EAN Code: 3389110845020



Main

| | |
|---------------------------|--|
| Range of product | Harmony XVB Universal |
| Product or component type | Base unit with cover |
| Component name | XVBC |
| Material | Glass reinforced polyamide: base unit Polycarbonate: cover unit |

Complementary

| | |
|-------------------------------|--|
| Fixing mode | Direct or tube fixing |
| Mounting diameter | 70 mm |
| Product destination | Banks without flash discharge tube unit |
| Electrical connection | 1 connector for standard input |
| Cable entry | Bottom or side entry |
| Assembly style | Customer assembly, up to 5 units |
| Terminals description ISO n°1 | (GND)GROUND (COM-1)PW (COM-4)PW (COM-3)PW (COM-5)PW (COM-2)PW |
| Net weight | 0.19 kg |

Environment

| | |
|-------------------------------------|---|
| Product certifications | CCC[RETURN]EAC[RETURN]CSA C22-2 No 14[RETURN]UL 508 |
| Standards | IEC 60947-5-1 |
| Protective treatment | TC |
| Ambient air temperature for storage | -40...70 °C |
| NEMA degree of protection | Type 4X conforming to UL (indoor) |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.500 cm |
| Package 1 Width | 10.000 cm |
| Package 1 Length | 9.500 cm |
| Package 1 Weight | 206.000 g |
| Unit Type of Package 2 | S03 |

| | |
|------------------------------|-----------|
| Number of Units in Package 2 | 36 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 8.173 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 288 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 71.516 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |


Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Indicator Bank without "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC..., to be ordered separately
- (3) Cover (supplied with base unit)

| Number of illuminated or audible signalling units (no "flash") | b in mm | b in in. |
|--|---------|----------|
| 1 | 138 | 5.43 |
| 2 | 201 | 7.91 |
| 3 | 264 | 10.39 |
| 4 | 327 | 12.87 |
| 5 | 390 | 15.35 |

Base Unit for Indicator Banks

Panel Cut-out for Direct Fixing



Illuminated Beacon

Wiring Diagram

