

Product data sheet

Characteristics

MGU3.501.12

Termostat Standard 8A,2M,Grafit



Principal

Gama	Unica
Denumire	Unica Top - Unica Class
Tip produs sau componenta	Termostat
Aplicatie a dispozitivului	Pardoseala
Prezentare dispozitiv	Mecanism
Culoare	Grafit

Suplimentar

Tip tehnologie	Electronic
[Ue] tensiune nominala de functionare	230 V c.a. +/- 10 % la 50/60 Hz
Curentul la intreruperea sarcinii	Inductiv:5 A Rezistiv:8 A
Tip de protectie	Protectie la suprasarcina termica
Numar module	2 module
Capacitate conexiune de prindere	$\leq 2 \times 2.5 \text{ mm}^2$ pentru flexibil cablu(ri) $\leq 2 \times 2.5 \text{ mm}^2$ pentru rigid cablu(ri)
Tip si compozitie contacte	1 C/O
Conexiuni - borne	Borne cu surub
Stare LED	1 LED bicolor (rosu/albastru) aplicatie de incalzire sau racire 1 LED (verde) prezenta tensiune
Marcaj	L+N
Temperatura programabila	Nu
Gama de setare a temperaturii	5...30 °C
Precizie de masurare	0,5 °C
Mod de fixare	Clipsare
Inaltime minima de montare	1,5 m
Adancime	45 mm
Latime	45 mm
Inaltime	45 mm
Adancime de montaj	33 mm
Greutate neta	0,083 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Grad de protectie IP	IP20
Grad de protectie IK	IK01
Temperatura ambientala de utilizare	5...30 °C
Temperatura ambietala pentru depozitare	-20...60 °C
Caracteristica de mediu	Fluid de curatare a geamurilor Acetona Benzina Alcool Rezistent UV Ulei Decolorant Sapun lichid
Standarde	EMC Directiva de compatibilitate electromagnetica EN 60730-2-9 Directiva de joasa tensiune

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,5 cm
Latime prima forma de impachetare	10,0 cm
Lungime prima forma de impachetare	10,9 cm
Greutate prima forma de impachetare	101,0 g
Unitate de masura pentru a doua forma de impachetare	S02
Numar unitati in a doua forma de impachetare	15
Inaltime a doua forma de impachetare	15,0 cm
Latime a doua forma de impachetare	30,0 cm
Lungime a doua forma de impachetare	40,0 cm
Greutate a doua forma de impachetare	1,865 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Directiva RoHS UE	Conform cu anumite exceptii
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Raport de mediu	 Profilul Ambiental Al Produsului
Profil circularitate	Nu sunt necesare operatii de reciclare speciale
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garanție contractuală

Garantie	18 months
----------	-----------