

Product data sheet

Characteristics

GCKRN50A2G

Exclusive - 2-pole switch with indicator lamp - 2 gangs - 50 A - white



Main

Product or component type	Switch with indicator lamp
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 5

Complementary

Switch function	2-pole
Control type	Dolly switch
Number of gangs	2 gangs
Pilot light	Red neon indicator
Device mounting	Wall mounted
Rated current	50 A at 230 V AC
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Surface finish	Matt
Height	86 mm
Width	146 mm
Depth	36 mm
Net weight	0.208 kg

Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------