

Product data sheet

Characteristics

LV429070

trip unit MicroLogic 2.2 for ComPact NSX
100/160/250 circuit breakers, electronic, rating
100A, 3 poles 3d



Important message: This product has been switched to new ComPacT range and is no longer commercialized.

Local distributor code: 391351578

EAN Code: 3606480016172



Main

Range	ComPact
Range of product	ComPact NSX100...250
Product or component type	Trip unit
Trip unit name	MicroLogic 2.2
Trip unit technology	Electronic
Range compatibility	ComPact NSX100 ComPact NSX160 ComPact NSX250
Device application	Distribution
Number of poles	3P
Protected poles description	3t
Trip unit protection functions	LSol
Protection type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Trip unit rated current	100 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	40...100 A
Long-time protection delay adjustment type tr	Fixed
[tr] long-time protection delay adjustment range	11 S at 7.2 x Ir 16 S at 6 x Ir 400 s at 1.5 x Ir
Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type Isd	Adjustable 9 settings
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Fixed
[tsd] Short-time protection delay adjustment range	0.02 s
Instantaneous protection pick-up adjustment type Ii	Fixed
[Ii] instantaneous protection pick-up adjustment range	1500 A
Earth-leakage protection	Without

Zone selective interlocking ZSI	Without
Local signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload

Environment

Standards	EN/IEC 60947-2 UL 508
Product certifications	EAC[RETURN]CCC[RETURN]Marine
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	9.2 cm
Package 1 Length	11 cm
Package 1 Weight	438 g
Unit Type of Package 2	S03
Number of Units in Package 2	28
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	13.238 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------