

Product data sheet

Characteristics

13182

Enclosure for power outlet, Mureva Enclosure, 1x18 modules, 8 openings 90x100mm, (W)448mm x (H)460mm, without term block



Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for power outlet
Mounting plate description	Without mounting plate

Complementary

Enclosure mounting	Surface
9 mm pitches	36
Number of 18 mm modules per row	18
Total number of 18 mm modules	19
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Number of openings of interface	8
Number of plates	2 for push-button controls 8 for 65 x 85 power outlets
Provided equipment	2 wiring strap 8 plate for 65 x 85 power outlet 2 plate for push-button control
Type of front cover	Transparent
Power dissipation in W	39 W
[In] rated current	90 A
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Locking options description	Optional keylock
Enclosure material	Housing: self-extinguishing polymer
Net weight	3.4 Kg
Base dimension	90 x 100 mm
Width	448 Mm
Height	460 Mm
Depth	160 Mm
Internal depth	91 Mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61439-3 EN 62262 EN 50262 IEC 60695-2-1 IEC 60670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	47.0 Cm
Package 1 Width	46.8 Cm
Package 1 Length	16.8 Cm
Package 1 Weight	3.35 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Height	80.0 Cm
Package 2 Width	80.0 Cm
Package 2 Length	120.0 Cm
Package 2 Weight	75.702 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product
Minimum percentage of recycled plastic content	24

Contractual warranty

Warranty	18 months
----------	-----------