

Product data sheet

Characteristics

04041

Linergy DX 4P distribution block 63A - 4 modules - 24 holes quick connect bottom



Principal

Gama	Linergy
Gama de produse	Prisma Plus System P Prisma Plus System G
Tip produs sau componenta	Bloc de distributie
Nume produs	Linergy DX
Compatibilitate gama	Prisma (Prisma G) Prisma (Prisma P) Prisma (Prisma PH) Prisma (Pack 160) Prisma (Prisma Pack 250)
Compatibilitate produs	Cabinet Spacial
Grad de protectie IP	IPxx B

Suplimentar

Locul conexiunii	Partea inferioara
Suport de montare	Sina DIN
Descriere poli	4P
[Ue] tensiune nominala de functionare	440 V c.a.
[Ui] tensiune nominala de izolatie	500 V c.a.
[Uimp] tensiune nominala de tinere la impuls	6 kV
[Ie] curent nominal de utilizare	63 A la 40 °C
[In] curent nominal	63 A la 40 °C
Conexiuni - borne	Alimentare terminal tip tunel16 mm ² (flexibil) Alimentare terminal tip tunel25 mm ² (rigid) Distributie bornă cu arc (faza) , 12 x 2,5...6 mm ² (flexibil) Distributie bornă cu arc (faza) , 12 x 2,5...6 mm ² (rigid) Distributie bornă cu arc (nul) , 12 x 2,5...6 mm ² (flexibil) Distributie bornă cu arc (nul) , 12 x 2,5...6 mm ² (rigid)
Numar de pasi de 9mm pe rand	8
Numarul total de module de 18 mm	4
Greutate neta	0,29 kg

Mediu

Grad de poluare	3
Rezistență la fir incandescent	960 °C conformitate cu IEC 60695-2-11
Standarde	IEC 60947-7-1 IEC 61439-2 IEC 61439-1
Certificari produs	ASEFA

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	7,6 cm
Latime prima forma de impachetare	8 cm
Lungime prima forma de impachetare	10,4 cm
Greutate prima forma de impachetare	316 g

Sustenabilitatea ofertei

Regulamentul REACH	 Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform  Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deeurilor si nu trebuie sa ajunga in pubelele de colectare a deeurilor menajere.