

Product data sheet

Characteristics

LC1D50JD

contactor TeSys Deca - 3 poles - AC-3 440V
50 A - coil 12 V DC



EAN Code: 3389110421477



Main

Range	TeSys
Range of product	TeSys Deca
Product or component type	Contacteur
Device short name	LC1D
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-2 AC-3 AC-1
Poles description	3P
[Ue] rated operational voltage	Power circuit: <= 690 V AC 25...400 Hz
[Ie] rated operational current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) DC AC-3 for power circuit 80 A (at <60 °C) DC AC-1 for power circuit
[Uc] control circuit voltage	380 V DC

Complementary

Motor power kW	25 KW at 415 V AC 50 Hz 30 KW at 440 V AC 50 Hz 30 KW at 500 V AC 50 Hz 33 KW at 660...690 V AC 50 Hz 15 KW at 220...230 V AC 50 Hz 30 KW at 1000 V AC 50 Hz 37 KW at 500 V AC 50 Hz 30 kW at 380...400 V AC 50 Hz
Motor power hp	7.5 Hp at 230/240 V AC 60 Hz for 1 phase motors 15 Hp at 200/208 V AC 60 Hz for 3 phases motors 15 Hp at 230/240 V AC 60 Hz for 3 phases motors 40 Hp at 460/480 V AC 60 Hz for 3 phases motors 40 Hp at 575/600 V AC 60 Hz for 3 phases motors 10 Hp at 230/240 V AC 60 Hz for 1 phase motors 5 hp at 115 V AC 60 Hz for 1 phase motors
Compatibility code	LC1D
Pole contact composition	3 NO
Protective cover	With
[Ith] conventional free air thermal current	80 A (at 60 °C) for power circuit 10 A (at 60 °C) for control circuit
Irms rated making capacity	900 A at 440 V DC for power circuit conforming to IEC 60947 1000 A at 440 V for power circuit conforming to IEC 60947 250 A DC for control circuit conforming to IEC 60947-5-1
Rated breaking capacity	1000 kA at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	520 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit

Associated fuse rating	100 A gG at ≤ 690 V coordination type 1 for power circuit 100 A gG at ≤ 690 V coordination type 2 for power circuit conforming to IEC 60947-5-1 125 A gG at ≤ 690 V coordination type 1 for power circuit 10 A gG for control circuit conforming to IEC 60947-5-1
Average impedance	1.5 Ohm - lth 80 A 50 Hz for power circuit
Power dissipation per pole	9.6 W AC-1 6.3 W AC-3
[Ui] rated insulation voltage	Control circuit: 600 V UL certified[RETURN]Power circuit: 600 V CSA certified[RETURN]Power circuit: 600 V UL certified conforming to IEC 60947-1[RETURN]Control circuit: 690 V conforming to IEC 60947-1[RETURN]Power circuit: 690 V CSA certified conforming to IEC 60947-1[RETURN]Control circuit: 600 V CSA certified
Overvoltage category	III
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Safety reliability level	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	10000000 cycles
Control circuit type	DC standard
Coil technology	Built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	0.75...1.25 Uc (-40...60 °C):operational DC 1...1.25 Uc (60...70 °C):operational DC 0.1...0.3 Uc (-40...70 °C):drop-out DC
Inrush power in W	19 W (at 20 °C)
Hold-in power consumption in W	7.4 W at 20 °C
Heat dissipation	4...5 W at 50/60 Hz for control circuit
Operating time	50 ±15 % ms closing 12...26 ms closing 4...19 ms opening
Maximum operating rate	3600 cyc/mn 60 °C
Connections - terminals	Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: rigid without cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...2.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm² - cable stiffness: flexible with cable end Power circuit: screw terminals 1 2.5...25 mm² - cable stiffness: rigid Power circuit: screw terminals 2 2.5...16 mm² - cable stiffness: rigid without cable end Power circuit: screw terminals 1 2.5...25 mm² - cable stiffness: flexible without cable end Power circuit: screw terminals 2 2.5...16 mm² - cable stiffness: flexible without cable end Power circuit: screw terminals 1 2.5...25 mm² - cable stiffness: flexible with cable end Power circuit: screw terminals 2 2.5...10 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: rigid Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: rigid
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminal - with screwdriver Philips No 2 Power circuit: 5 N.m - on screw terminal - with screwdriver flat Ø 6 to Ø 8 mm Control circuit: 1.7 N.m - on screw clamp terminal - with screwdriver pozidriv No 2 Control circuit: 1.7 N.m - on screw clamp terminal - with screwdriver flat Ø 6 mm
Auxiliary contact composition	1 NO + 1 NC
Auxiliary contacts type	Type mirror contact 1 NC conforming to IEC 60947-4-1 Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1
Minimum switching voltage	17 V for control circuit
Minimum switching current	5 mA for control circuit
Insulation resistance	> 10 MOhm for control circuit
Non-overlap time	1.5 Ms on energisation between NC and NO contacts 1.5 ms on de-energisation between NC and NO contacts
Mounting support	Rail Plate

Environment

Standards	EN 60947-5-1 IEC 60947-5-1 EN 60947-4-1 CSA C22.2 No 14 IEC 60947-4-1
Product certifications	LROS (Lloyds register of ship- ping)[RETURN]CCC[RETURN]RINA[RETURN]GL[RETURN]GOST[RETURN]DNV[RETURN]U
IP degree of protection	IP2X conforming to VDE 0106 IP2X conforming to IEC 60529
Protective treatment	TH (pollution degree 3) conforming to IEC 60068-2-30
Climatic withstand	Conforming to IACS E10 exposure to damp heat
Operating altitude	0...3000 m
Fire resistance	850 °C conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Shocks contactor closed (15 Gn for 11 ms) Vibrations contactor opened (2 Gn, 5...300 Hz) Vibrations contactor closed (4 Gn, 5...300 Hz) Shocks contactor opened (10 Gn for 11 ms)
Height	122 mm
Width	70 mm
Depth	118 mm
Net weight	2.185 kg
Quantity per set	Set of 1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	14.5 cm
Package 1 Length	9 cm
Package 1 Weight	2.182 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------