



Product data sheet

Characteristics

GV2LC0216

enclosed DOL starter TeSys - GV2-LC - 14 A

EAN Code: 3389110948240

Main

Range of product	TeSys
Device short name	GV2LC
Motor starter type	Non reversing
Product or component type	Enclosed DOL starter
Poles description	3P
Motor starter composition	With circuit breaker
Trip unit technology	Magnetic
Thermal protection adjustment range	14 A
Control type	Rotary handle black
Enclosure material	Polycarbonate

Complementary

[Ue] rated operational voltage	690 V
Breaking capacity	10 kA Icu at 500 V conforming to IEC 60947-2 100 kA Icu at 220...230 V conforming to IEC 60947-2 20 kA Icu at 440 V conforming to IEC 60947-2 50 kA Icu at 400...415 V conforming to IEC 60947-2
Magnetic tripping limit	13 x In +/- 20 %
Cable entry	2 x 20 mm ISO at bottom 2 x 20 mm ISO at top 2 x 25 mm ISO at bottom 2 x 25 mm ISO at top
Locking options description	1 to 3 padlocks Ø 8 Padlock in OFF position
Width	88 mm
Height	166 mm
Depth	173 mm
Net weight	0.78 kg

Environment

Standards	VDE 0660-102 EN 60947 IEC 60439-1 IEC 60947-4
IP degree of protection	IP547 conforming to IEC 60529

Contractual warranty

Warranty	18 months
----------	-----------