

Product data sheet

Characteristics

LC3K06U7

TeSys K - star delta starter - 3 x 3P (3 NO) - 6 A - 240 V AC coil



EAN Code: 3389110282849



Main

Range	TeSys
Product name	TeSys K
Product or component type	Star delta starter
Device short name	LC3K
Contactor application	Motor control
Utilisation category	AC-3
Device presentation	Pre-wired
Poles description	3 x 3P
Power pole contact composition	3 x 3 NO
[Ue] rated operational voltage	Power circuit: ≤ 690 V AC 25...400 Hz
[Ie] rated operational current	6 A (at ≤ 50 °C) at ≤ 440 V AC AC-3 for power circuit
Motor power kW	3 kW at 220/230 V AC 50/60 Hz 5.5 kW at 380/400 V AC 50/60 Hz 5.5 kW at 415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	240 V AC 50/60 Hz
Auxiliary contact composition	1 NC for KM1 star contactor
[Uimp] rated impulse withstand voltage	8 kV
Overtoltage category	III
[Ui] rated insulation voltage	Power circuit: 750 V conforming to VDE 0110 group C Power circuit: 690 V conforming to IEC 60947 Power circuit: 690 V conforming to BS 5424 Power circuit: 690 V conforming to NF C 20-040 Power circuit: 600 V CSA 22-2 certified Power circuit: 600 V UL 508 certified Signalling circuit: 750 V conforming to VDE 0110 group C Signalling circuit: 690 V conforming to IEC 60947 Signalling circuit: 690 V conforming to BS 5424 Signalling circuit: 690 V conforming to NF C 20-040 Signalling circuit: 600 V CSA 22-2 certified Signalling circuit: 600 V UL 508 certified
Electrical durability	1.3 Mcycles 6 A AC-3 at Ue ≤ 440 V
Interlocking type	Mechanical
Mounting support	Rail
Standards	VDE 0660 IEC 60947 NF C 63-110

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Connections - terminals	Screw clamp terminals 1 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 1 0.75...4 mm ² - cable stiffness: flexible without cable end Screw clamp terminals 1 0.34...2.5 mm ² - cable stiffness: flexible with cable end Screw clamp terminals 2 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 2 0.75...4 mm ² - cable stiffness: flexible without cable end Screw clamp terminals 2 0.34...1.5 mm ² - cable stiffness: flexible with cable end
Tightening torque	1.3 N.M - on screw clamp terminals - with screwdriver Philips No 2 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
Mechanical durability	10 Mcycles
Maximum operating rate	12 cyc/h 60 °C
Starting time	30 s
Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational: 0.8...1.15 U _c (at <50 °C) Drop-out: 0.2...0.75 U _c (at <50 °C)
Inrush power in VA	30 VA (at 20 °C)
Hold-in power consumption in VA	4.5 VA (at 20 °C)
Heat dissipation	1.3 W
Auxiliary contacts type	Mechanically linked conforming to IEC 60947-5-1 3 x 1 NO + 1 NC Mirror contact conforming to IEC 60947-4-1 3 x 1 NC
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Width	150 mm
Height	110 mm
Depth	94 mm
Net weight	0.74 kg

Environment

Insulation resistance	> 10 MOhm for signalling circuit
IP degree of protection	IP2X conforming to VDE 0106
Protective treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient air temperature for storage	-50...80 °C
Operating altitude	2000 m without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 4 Gn, 5...300 Hz Shocks contactor closed, on X axis: 10 Gn for 11 ms Shocks contactor opened, on X axis: 6 Gn for 11 ms Shocks contactor closed, on Y axis: 15 Gn for 11 ms Shocks contactor opened, on Y axis: 10 Gn for 11 ms Shocks contactor closed, on Z axis: 15 Gn for 11 ms Shocks contactor opened, on Z axis: 10 Gn for 11 ms

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	18.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.751 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------