

Product data sheet

Characteristics

NSYMP128

Spacial SF/SM mounting plate - 1200x800 mm



Local distributor code: 385515139

EAN Code: 3606485126777



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 1200 mm W: 800 mm
Mounting plate description	Plain
Range compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device composition	1 mounting plate 2 sliding shoes
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m ²
Permanent permissible load	500 Kg intermediate position 600 kg back of the enclosure
Height	1050 Mm fixing centers: 1200 Mm nominal: 1097 mm real:
Width	800 Mm nominal: 650 Mm fixing centers: 696 mm real:
Depth	27 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	70.5 cm
Package 1 Length	111.0 cm
Package 1 Weight	18.0 kg
Unit Type of Package 2	P12
Number of Units in Package 2	20
Package 2 Height	74.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	373.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------