

## Product data sheet

### Characteristics

# NSYMP168

Spacial SF/SM mounting plate - 1600x800 mm



Local distributor code: 385515142

EAN Code: 3606485126814



### Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	- H: 1600 mm W: 800 mm
Mounting plate description	Plain
Range compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device composition	1 mounting plate 2 sliding shoes
Quantity per set	Set of 1
Material	Galvanised steel

### Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m <sup>2</sup>
Permanent permissible load	500 Kg intermediate position 600 kg back of the enclosure
Height	Fixing centers: 1450 mm Nominal: 1600 mm Real: 1497 mm
Width	Nominal: 800 mm Fixing centers: 650 mm Real: 696 mm
Depth	27 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	70.0 cm
Package 1 Length	151.5 cm
Package 1 Weight	27.0 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Height	80.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	540.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------