


Product data sheet

Characteristics

VW3A4671

passive filter - 370 A - 460 V - for variable speed drive

EAN Code: 3389119204644



Main

Product or component type	Passive filter
Product specific application	Reduction of current harmonics

Complementary

Range compatibility	Altivar 71 Altivar 61
[Us] rated supply voltage	480 V +/- 10 %
Power supply frequency	60 Hz +/- 5 %
Quantity per drive	1 filter per drive for ATV61HC22N4 1 filter per drive for ATV71HC20N4 1 filter per drive for ATV71HC25N4 2 filters per drive for ATV61HC50N4 2 filters per drive for ATV71HC50N4
[In] rated current	370 A
Network number of phases	3 phases
THDI	5 % for ATV71HC25N4 ATV71H motor: 250 kW/400 hp 5 % for ATV61HC50N4 ATV61H motor: 500 kW/700 hp 5 % for ATV71HC50N4 ATV71H motor: 500 kW/700 hp 5 % for ATV61HC22N4 ATV61H motor: 220 kW/350 hp 5 % for ATV71HC20N4 ATV71H motor: 200 kW/300 hp
Max current	1.5 x nominal current
Efficiency	98 %
Cos phi	1 (150 % of line current) 0.85 (75 % of line current) 0.99 (100 % of line current)
Electrical connection	Bare wires diameter: 16.5 mm
Electrical insulation class	Class F
Net weight	250 kg

Environment

IP degree of protection	IP20
Relative humidity	5...85 % without condensation
Ambient air temperature for operation	40...55 °C (with current derating 3 % per °C) 5...40 °C (without current derating)
Ambient air temperature for storage	-25...55 °C
Operating altitude	<= 1000 m without current derating > 1000...4000 m with current derating 5 % per 1000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------