

# Product data sheet


## Characteristics

# NSY2SP205

Spacial SF external fixing side panels -  
2000x500 mm



Local distributor code: 1917655  
EAN Code: 3606485119946



### Main

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Range                              | Spacial                             |
| Accessory / separate part category | Enclosure accessory                 |
| Product or component type          | Side panel                          |
| Application                        | Prisma application<br>Multi-purpose |
| For enclosure nominal dimensions   | -                                   |
| Mounting location                  | Sides of enclosure                  |
| Quantity per set                   | Set of 1                            |

### Complementary

|                     |   |
|---------------------|---|
| Range compatibility | Spacial Spacial SF  |
| Device composition  | Fixing elements<br>2 side panel   |
| Material            | Steel   |
| Colour              | Grey (RAL 7035)   |
| Surface finish      | Epoxy-polyester powder  |
| Fixing mode         | By screws - screw type captive - from the outside of enclosure location |
| Height              | Nominal: 2000 mm  |
| Width               | Nominal: 500 mm   |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 6.500 cm   |
| Package 1 Width              | 49.000 cm  |
| Package 1 Length             | 201.000 cm |
| Package 1 Weight             | 27.000 kg  |
| Unit Type of Package 2       | PAL        |
| Number of Units in Package 2 | 20         |
| Package 2 Height             | 78.000 cm  |
| Package 2 Width              | 203.000 cm |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 570.000 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

## Logistical informations

|                   |    |
|-------------------|----|
| Country of origin | US |
|-------------------|----|

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|