

Product data sheet

Characteristics

TCSECN300R2

ConneXium Ethernet copper cable for Ethernet network - 300 m

Local distributor code: 393519402

EAN Code: 3595863925470



Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Ethernet copper cable
Accessory / separate part destination	Ethernet network
Cable length	300 m
Cable packaging	Roll

Complementary

Transmission rate	100 Mbit/s 80 m
Transmission support medium	Double shielded twisted pair
AWG gauge	AWG 24
Marking	CE
Conductor material	Copper

Environment

Standards	EN 50173 class D UL 508-CM EIA/TIA-568 category CAT 5E
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	37.0 cm
Package 1 Length	37.0 cm
Package 1 Weight	13.32 kg
Unit Type of Package 2	P12
Number of Units in Package 2	10
Package 2 Height	65.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	133.2 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------