

Product data sheet

Characteristics

XGCS4901201

RFID compact smart antenna - 13.56MHz - flat form 40x40x15 - M12 - cable 0.2m



Important message: We have updated the process for ordering Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative in the UK&I at: UK.salesorders@tesensors.com. You can find all product information on the Telemecanique Sensors website: www.tesensors.com/uk/en
Local distributor code: 389942481
EAN Code: 3389119021227



Main

Range of product	Telemecanique Radio frequency identification XG
Product or component type	Compact smart antenna
RFID compact station name	XGCS
RFID frequency	13.56 MHz
Design	Flat form 40 x 40 x 15
Electrical connection	5 pin(s) male remote connector M12, shielded cable cable 0.2 m
Transmission rate	9600 bauds...115200 bauds (automatic detection)
Outer dimension	40 x 40 x 15 mm
Product compatibility	RFID microchip Microelectronic (EM4135) RFID microchip Texas (Tag-it HFI) RFID microchip NXP (SL2, SL1, Ultralight, Std 1K/4K, Desfire) RFID microchip STM (CR1X4K) RFID microchip INSIDE (micropass) RFID microchip Fujitsu (MB89R118 - MB89R119)
[Sn] nominal sensing distance	10...70 mm
[Us] rated supply voltage	24 V DC conforming to Protective Extra Low Voltage

Complementary

Communication port protocol	Modbus RTU Uni-Telway
Communication port support	RS485
Associated tag type	Automatic detection of the type of tag ISO 14443 standard tags ISO 15693 standard tags
Supply voltage limits	19.2...29 V DC
Current consumption	< 60 mA
Status LED	Communication network: 1 LED (dual colour) RFID communication: 1 LED (dual colour)
Tightening torque	< 1 N.m
Marking	CE
Net weight	0.057 kg

Environment

Product certifications	UL, FCC
Standards	ETSI EN 301 489-3 ETSI EN 300 330-1 ETSI EN 301 489-1 ETSI EN 300 330-2
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
IP degree of protection	IP65 conforming to IEC 60529
Vibration resistance	2 mm (f= 5...29.5 Hz) conforming to IEC 60068-2-6 7 gn (f= 29.5...150 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn for 11 ms conforming to IEC 60068-2-27
IK degree of protection	IK02 conforming to IEC 62262
Electromagnetic compatibility	Electrostatic discharge immunity test: (contact discharge), 3, 6 kV, conforming to IEC 61000-4-2 Electrostatic discharge immunity test: (air discharge), 3, 8 kV, conforming to IEC 61000-4-2 Electrical fast transient/burst immunity test: (signal ports), 3, 1 kV, conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test: (power ports), 3, 2 kV, conforming to IEC 61000-4-4 Susceptibility to electromagnetic fields: , 3, 10 V/m, conforming to IEC 61000-4-3 1.2/50 µs shock waves immunity test: , 3, 10 kV, conforming to IEC 61000-4-5 Conducted RF disturbances: , 3, 10 V, conforming to IEC 61000-4-6 Magnetic field at power frequency: , 4, 30 A/m, conforming to IEC 61000-4-8

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	4.000 cm
Package 1 Length	9.500 cm
Package 1 Weight	82.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	44
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.927 kg

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions


Compact Smart Antennas



- (1) 4 x Ø 4.5. for CHC type screws
- (2) Shielded cable (length: 20 cm)
- (3) A-coded, male 5-pin M12 connector


Minimum Mounting Distances

Distance Between Smart Antennas



Tag	e1	e2	e3
XGHB90E340 XGHB520246	310	550	120
XGHB221346	200	320	100
XGHB320***	140	360	110
XGHB211345 XGHB123345	210	180	60
XGHB44***	90	190	30


Minimum Mounting Distances in a Metal Structure



(e) ≥ 20 mm.

Wiring Diagram


Modbus Connections



Pin no.	Modbus smart antenna signal
1	Drain (Modbus-SHLD)
2	+ 24 VDC
3	0 V/Modbus-GND
4	D0
5	D1
Connector casing	Shielding

Curves

Dialogue Zones of Compact Smart Antennas



(1) Recommended movement zone: between 0.4 and 0.8 Pn.