

## Product data sheet

### Characteristics

# XGHB123345

Electronic tag, Radio frequency identification  
XG, RFID 13.56 MHz, cylindrical Ø 12, 304  
Bytes

Important message: We have updated the process for ordering Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative in the UK&I at: [UK.salesorders@tesensors.com](mailto:UK.salesorders@tesensors.com). You can find all product information on the Telemecanique Sensors website: [www.tesensors.com/uk/en](http://www.tesensors.com/uk/en)  
EAN Code: 3389119061827



### Main

Range of product	Telemecanique Radio frequency identification XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	Cylindrical M12
Memory capacity	304 B
Associated smart antenna	XGCS
[Sn] nominal sensing distance	18 Mm with XGCS49 20 Mm with XGCS89 20 mm with XGCS85
Outer dimension	Ø12 x 8 mm
Quantity per set	Set of 5
Read time	12 + 0.825 x (number of 16-bit words) ms
Write time	19 + 4.1 x (number of 16-bit words) ms
IP degree of protection	IP68
Fixing mode	By screws

### Complementary

Memory type	EEPROM
Memory operation	Read/write
Number of read cycles	Unlimited
Number of write cycles	100000 at -25...70 °C 2500000 at 30 °C
Maximum linear speed with "auto read/write function"	1.8 M/S with XGCS49 (read a serial number) 0.6 M/S with XGCS49 (read a word) 0.2 M/S with XGCS49 (read or write 10 words) 3 M/S with XGCS89 (read a serial number) 0.9 M/S with XGCS89 (read a word) 0.4 M/S with XGCS89 (read or write 10 words) 3 M/S with XGCS85 (read a serial number) 0.9 M/S with XGCS85 (read a word) 0.4 m/s with XGCS85 (read or write 10 words)
Data retention time	10 year(s)
Material	PBT (polybutylene terephthalate)
Net weight	0.02 kg




## Environment

Standards	ISO 15693
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	2 mm conforming to IEC 60068-2-6 (f = 5...29.5 Hz) 7 gn conforming to IEC 60068-2-6 (f = 29.5...150 Hz)
Shock resistance	30 gn conforming to IEC 60068-2-27 for 11 ms
IK degree of protection	IK02 conforming to IEC 62262

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	4.000 cm
Package 1 Length	4.500 cm
Package 1 Weight	0.900 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	1.500 cm
Package 2 Width	4.000 cm
Package 2 Length	4.500 cm
Package 2 Weight	7.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	341.000 g

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty


Warranty	18 months
----------	-----------

---

Dimensions


---

Updatable Code Electronic Tags



Minimum Mounting Distances

Distance Between Tags



XGCS4901201 smart antenna (format 40)		XGCS8•• smart antennas (format 80)	
e1	e2	e1	e2
40	10	120	20

Minimum Mounting Distances in a Metal Structure

No metal parts within 25 mm of the tag