


Product data sheet

Characteristics

XGSZ22E4510

Ethernet copper cable, Radio frequency identification XG, Jumper M12/RJ45 straight/ elbowed shielded 10 m

Important message: We have updated the process for ordering Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative in the UK&I at: UK.salesorders@tesensors.com. You can find all product information on the Telemecanique Sensors website: www.tesensors.com/uk/en
EAN Code: 3389119086080



Main

Range of product	Telemecanique Radio frequency identification XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Ethernet copper cable
Product compatibility	XGSZ33ETH XUW XGSZ33EIP
Accessory / separate part destination	Ethernet network

Complementary

Cable length	10 m
Transmission rate	100 Mbit/s
Transmission support medium	2 twisted shielded pairs
Communication network category	5e
AWG gauge	AWG 26
Electrical connection	1 male connector, RJ45 straight connector with 4 pin(s) 1 male connector, M12 elbowed connector with 4 pin(s) - encoding type: D coding
Conductor material	Copper
Cover material	PUR
Net weight	0.43 kg

Environment



IP degree of protection	IP67
Standards	EIA/TIA-568 IEC 60754-1 ISO/IEC 11801 Ed.2, 2002

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	18.000 cm
Package 1 Length	19.000 cm
Package 1 Weight	471.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	15 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.118 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

