

## Product data sheet

### Characteristics

# ZB4BC38036RA

pushbutton head for harsh environment - green  
- with marking-legend rotated 90°



EAN Code: 3606480444548



### Main

|                               |                       |
|-------------------------------|-----------------------|
| Range of product              | Harmony XB4           |
| Product or component type     | Head for push-button  |
| Device short name             | ZB4                   |
| Bezel material                | Chromium plated metal |
| Head type                     | Standard              |
| Mounting diameter             | 22 mm                 |
| Sale per indivisible quantity | 1                     |

### Complementary

|                                   |                                                                                                                                                                                                                                                           |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width                 | 37 mm                                                                                                                                                                                                                                                     |
| CAD overall height                | 18.5 mm                                                                                                                                                                                                                                                   |
| CAD overall depth                 | 37 mm                                                                                                                                                                                                                                                     |
| Net weight                        | 0.036 kg                                                                                                                                                                                                                                                  |
| Electrical shock protection class | Class I conforming to IEC 61140                                                                                                                                                                                                                           |
| Shape of signaling unit head      | Round                                                                                                                                                                                                                                                     |
| Type of operator                  | Spring return                                                                                                                                                                                                                                             |
| Operator profile                  | Green flush, type H036 (white)                                                                                                                                                                                                                            |
| Operator additional information   | Horizontal mounting                                                                                                                                                                                                                                       |
| Mechanical durability             | 3000000 cycles                                                                                                                                                                                                                                            |
| Vibration resistance              | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                                                                                                          |
| Shock resistance                  | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27                                                                                                                                                                     |
| Main group                        | Harsh environment                                                                                                                                                                                                                                         |
| Group of product                  | Flush marked type H036                                                                                                                                                                                                                                    |
| Cap/operator or lens colour       | Green                                                                                                                                                                                                                                                     |
| Marking                           | Type H036                                                                                                                                                                                                                                                 |
| Colour of marking                 | White                                                                                                                                                                                                                                                     |
| Electrical composition code       | C1 for <9 contacts using single blocks in front mounting<br>C2 for <9 contacts using single and double blocks in front mounting<br>C11 for <3 contacts using single blocks in front mounting<br>C15 for <1 contacts using single blocks in front mounting |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                       |                                                     |
|---------------------------------------|-----------------------------------------------------|
| Ambient air temperature for storage   | -40...85 °C                                         |
| Ambient air temperature for operation | -40...70 °C                                         |
| IP degree of protection               | IP66 conforming to IEC 60529<br>IP69K<br>IP69       |
| NEMA degree of protection             | NEMA 4 conforming to UL 508<br>NEMA 13<br>NEMA 12   |
| Resistance to high pressure washer    | 90 Pa at 82.5 °C                                    |
| IK degree of protection               | IK06 conforming to IEC 62262                        |
| Standards                             | IEC 60947-5-1<br>IEC 60947-1<br>UL 508<br>CSA C22.2 |
| Product certifications                | UL[RETURN]CE[RETURN]CSA                             |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.76 cm |
| Package 1 Width              | 3.7 cm  |
| Package 1 Length             | 3.7 cm  |
| Package 1 Weight             | 36.0 g  |

## Offer Sustainability

|                            |                                                                                                |
|----------------------------|------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                          |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                              |
| REACH free of SVHC         | Yes                                                                                            |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                                                                            |
| Mercury free               | Yes                                                                                            |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                            |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                  |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                        |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---

Dimensions

---



## Installation on Flat Surface

### Without Protective Guard



(1) Ø22.5 mm recommended ( $\text{Ø}22.3_0^{+0.4}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88_0^{+0.016}$ )

### With Protective Guard



(1) Ø22.5 mm recommended ( $\text{Ø}22.3_0^{+0.4}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88_0^{+0.016}$ )

---

Marking Type H036

---



---

Electrical Composition Corresponding to Code C1

---



---

Electrical Composition Corresponding to Code C2

---



---

Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1

---



---

Electrical Composition Corresponding to Code C15

---

1 N/O



1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



## Legend

---

Single contact



Double contact



Light block



Possible location

