

## Product data sheet

### Characteristics

## XVLA314

LED pilot light with integral lens cap, Harmony XVL, Ø 12, IP40/IP65, red, covered included, 5 V, lugs



EAN Code: 3389110651560



### Main

Range of product	Harmony XVL
Product or component type	LED pilot light with integral lens cap
Component name	XVL
Mounting diameter	12 mm
Light source	Covered LED
Light block colour	Red
Protection type	Integral ballast resistor Built-in by diode
[Us] rated supply voltage	5 V
IP degree of protection	IP65 (with seal XVLZ912) conforming to IEC 60529 IP65 (with seal XVLZ912) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010

### Complementary

Supply circuit type	DC
Connections - terminals	Threaded connector: clamping capacity 1 x 0.2...1 x 1.5 mm <sup>2</sup>
Current consumption	25 mA
[Ui] rated insulation voltage	50 V conforming to IEC 60947-1
Bulb lifespan	100000 h
Nominal voltage limit	0.8...1.1 Un
Terminals description ISO n°1	(X1-X2)PL
Height	16 mm
Width	16 mm
Depth	51 mm
Net weight	0.007 kg

### Environment

Product certifications	UL[RETURN]CSA
Protective treatment	TC
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Overvoltage category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	1.5 cm
Package 1 Length	5.0 cm
Package 1 Weight	7.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	15.0 cm
Package 2 Length	13.0 cm
Package 2 Weight	73.0 g
Unit Type of Package 3	S01
Number of Units in Package 3	50
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	574.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty


Warranty	18 months
----------	-----------

---

LED Pilot Light

---


Dimensions



- (1) Threaded connector  
e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
12.2	0.48	16.5	0.65	16.5	0.65