

Product data sheet

Characteristics

XVLA394

pilot light Ø12 - IP40/IP65 - red - covered LED
included - ≤ 30 mA - lugs



Main

Range of product	Harmony XVL
Product or component type	LED pilot light with integral lens cap
Component name	XVL
Mounting diameter	12 mm
Light source	Covered LED
Light block colour	Red
Protection type	Without protection
IP degree of protection	IP65 (with seal XVLZ912) conforming to IEC 60529 IP65 (with seal XVLZ912) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010

Complementary

Input current	30 mA DC
Connections - terminals	Threaded connector: clamping capacity 1 x 0.2...1 x 1.5 mm ²
[Ui] rated insulation voltage	50 V conforming to IEC 60947-1
Bulb lifespan	100000 h
Terminals description ISO n°1	(X1-X2)PL
Height	16 mm
Width	16 mm
Depth	51 mm
Net weight	0.007 kg

Environment


Product certifications	UL[RETURN]CSA
Protective treatment	TC
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Overvoltage category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	1.6 cm
Package 1 Length	4 cm
Package 1 Weight	7 g

LED Pilot Light


Dimensions



- (1) Threaded connector
e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
12.2	0.48	16.5	0.65	16.5	0.65