

## Product data sheet

### Characteristics

# XZCB4L1000

PvR cable - 4 x 0.5 mm<sup>2</sup> - length 1000 m

Important message: We have updated the process for ordering Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative in the UK&I at: [UK.salesorders@tesensors.com](mailto:UK.salesorders@tesensors.com). You can find all product information on the Telemecanique Sensors website: [www.tesensors.com/uk/en](http://www.tesensors.com/uk/en)  
EAN Code: 3389110197273



### Main

Accessory / separate part type	Cable
--------------------------------	-------

### Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	1000 m
Material	PvR (PVC/NBR) sheath
Colour	Matt black
Cable cross section	0.5 mm <sup>2</sup>
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V conforming to NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm <sup>2</sup>
Hardness	70 shores A (tolerance: +/-5)
Net weight	46.3 kg

### Environment

Ambient air temperature for operation	-35...90 °C
Ambient air temperature for storage	-40...100 °C
Environmental characteristic	Without un moulding agent Synthetic oils at 90 °C Mineral resistant at 90 °C Soluble resistant at 90 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------