

LUA1C11TQ

Auxiliary contact, TeSys Ultra, 1NO + 1NC, 0 to 250VAC/DC, for Fault signalling, set of 10



Main

Range	TeSys
Device short name	LUA1
Product or component type	Auxiliary contact
Quantity per set	Set of 10

Complementary


Auxiliary contact composition	1 NO + 1 NC
Signalling function	Fault signalling Indicating rotary knob in ready position
[Ue] rated operational voltage	<= 250 V AC <= 250 V DC
[Ui] rated insulation voltage	250 V conforming to CSA 250 V conforming to IEC 60947-5-1 250 V conforming to UL
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Net weight	0.03 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	20.5 cm
Package 1 Length	29.0 cm
Package 1 Weight	705.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	7.5 cm
Package 2 Width	20.5 cm
Package 2 Length	29.0 cm
Package 2 Weight	14.1 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months