

LV431390

Circuit breaker basic frame, ComPact
NSX250B, 25kA at 415VAC 50/60 Hz, 250A,
without trip unit, 3 poles



Main

Range	ComPact
Range of product	ComPact NSX100...250
Device short name	NSX250B
Product or component type	Basic frame
Device application	Distribution
Circuit breaker name	Compact NSX250B
Number of poles	3P
[In] rated current	250 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	15 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	B 25 kA 415 V AC
Control type	Toggle
Mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	20 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 KA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 ka at 500 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	20000 cycles conforming to IEC 60947-2
Electrical durability	10000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 10000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 20000 Cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 5000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Connection pitch	35 mm
Protection type	Without protection
Width (W)	105 mm
Height (H)	161 mm
Depth (D)	86 mm

Environment

Standards	EN/IEC 60947-2 UL 508
Product certifications	CSA[RETURN]UL
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	13.7 cm
Package 1 Length	19.5 cm
Package 1 Weight	1.58 kg
Unit Type of Package 2	S04
Number of Units in Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	24.586 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	50.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	111.544 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------