



Main

Range	Spacial
Extended range	Spacial SF
Application	PC application
Product or component type	Suitable enclosure
Enclosure nominal height	1600 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	600 mm
Enclosure mounting	Floor-standing
Product specific application	Protecting computer equipment
Device composition	1 structure 1 roof 2 side panels 1 cable gland plate 1 partial door for keyboard 1 partial door for PC screen 1 partial door for printer support 1 rear door

Complementary

Structure type	Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure Vertical uprights joined with top and bottom frames
Door type	Plain partial front Glazed partial front Plain rear
Number of doors	Front: 3 door(s) Rear: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	Flat escutcheon lock, 5 mm double bar rear door Escutcheon lock, 3 mm double bar front partial doors
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry
Number of compartments	3
Accessibility for operation	Rear Front Sides of enclosure
Removable parts	Roof by screws internally Side panel by screws internally Door by screws hinge
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Escutcheon: polyamide 6 with 30 % fibre glass

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 (of transparent door) IK10 conforming to IEC 62262 (of plain door)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------