

VCFN32GE

TeSys Vario enclosed, emergency stop switch disconnecter, 25A, IP55



Main

Range	TeSys
Product name	TeSys Mini-VARIO
Device short name	VCFN
Product or component type	Emergency stop switch disconnecter
Performance level	Standard
Poles description	3P
Control type	Rotary handle
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 4...8 mm

Complementary

Marking	0 - 1
[Ue] rated operational voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ithe] conventional enclosed thermal current	25 A
[Ie] rated operational current	21.8 A (AC-23A) at 400 V
Rated operational power in W	11 kW at 400 V (AC-23) 7.5 kW at 400 V (AC-3)
Intermittent duty class	30
Making capacity (I Rms)	320 A at 400 V AC-21A
[Icw] rated short-time withstand Rms current	384 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V
Suitability for isolation	Yes
Fire resistance	960 °C conforming to IEC 60595-2-1
Handle front plate dimension	60 x 60 mm
Height	131 mm
Width	82.5 mm
Depth	106 mm
Net weight	0.512 kg

Environment

Standards	IEC 60947-4-1
Protective treatment	TC
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------