

Product data sheet

Characteristics

VZN14

TeSys Mini-VARIO - additional earthing block -20 A - for VN12, VN-20



Main

Range	TeSys
Device short name	VZN
Product or component type	Additional earthing block
Performance level	Standard
Product compatibility	VN12 VN20
Network type	DC AC
Network frequency	50/60 Hz
Mounting location	Right

Complementary

Range compatibility	TeSys VARIO VCFN switch disconnecter
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	20 A
Mechanical durability	50000 cycles
Electrical durability	30000 Cycles DC-11 50000 cycles AC-21
Connections - terminals	Screw clamp terminals
Height	45.5 mm
Width	12 mm
Depth	39 mm
Net weight	0.016 kg

Environment

Standards	IEC 60947-3
Product certifications	CSA UL GL
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (5 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------