

Product data sheet

Characteristics

LC1D40004R7

contactor - TeSys LC1-D - 4 poles - AC-1 440V
60 A - coil 440V AC



Main

Range of product	TeSys D
Product or component type	Contacteur
Device short name	LC1D
Contacteur application	Resistive load
Utilisation category	AC-1
Control circuit type	AC
Coil type	Standard
Poles description	4P
Pole contact composition	4 NO
[Ie] rated operational current	60 A (at <60 °C) AC AC-1 for power circuit
[Uc] control circuit voltage	440 V AC 50/60 Hz
Connections - terminals	Control circuit: screw clamp terminal 1 x 1... 4 mm ² solid without cable end Control circuit: screw clamp terminal 2 x 1... 2.5 mm ² flexible with cable end Control circuit: screw clamp terminal 2 x 1... 4 mm ² flexible without cable end Control circuit: screw clamp terminal 2 x 1... 4 mm ² solid without cable end Power circuit: screw clamp terminal 1 x 1... 35 mm ² solid without cable end Power circuit: screw clamp terminal 2 x 1... 25 mm ² solid without cable end Power circuit: screw clamp terminal 2 x 1... 35 mm ² solid without cable end

Complementary

Coil technology	Without built-in bidirectional peak limiting diode suppressor
Protective cover	With
Auxiliary contacts type	Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 Type mirror contact 1 NC conforming to IEC 60947-4-1
Control circuit voltage limits	Drop-out: 0.3...0.6 U _c at 50/60 Hz (at <60 °C) Operational: 0.8...1.1 U _c at 50 Hz (at <60 °C) Operational: 0.85...1.1 U _c at 60 Hz (at <60 °C)
[Ui] rated insulation voltage	Control circuit: 600 V CSA certified Control circuit: 600 V UL certified Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Control circuit: 690 V conforming to IEC 60947-1 Power circuit: 690 V conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overvoltage category	III
Mounting support	Plate Rail
Flame retardance	V1 conforming to UL 94
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminal - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminal - with screwdriver Philips No 2 Power circuit: 5 N.m - on screw clamp terminal - with screwdriver flat Ø 6 mm Power circuit: 5 N.m - on screw clamp terminal - with screwdriver flat Ø 8 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

[Ue] rated operational voltage	Power circuit: ≤ 690 V AC 25...400 Hz
[Ith] conventional free air thermal current	10 A (at 60 °C) for control circuit 60 A (at 60 °C) for power circuit
Irms rated making capacity	140 A AC for control circuit conforming to IEC 60947-5-1 800 A at 440 V for power circuit conforming to IEC 60947
Rated breaking capacity	800 A at 440 V for power circuit conforming to IEC 60947
Associated fuse rating	10 A gG for control circuit conforming to IEC 60947-5-1 80 A gG at ≤ 690 V coordination type 1 for power circuit 80 A gG at ≤ 690 V coordination type 2 for power circuit
Average impedance	- Ith 60 A 50 Hz for power circuit
Power dissipation per pole	5.4 W AC-1
Inrush power in VA	140 VA cos phi 0.75 (at 20 °C) 160 VA cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Operating time	12...26 ms closing 4...19 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	6000000 cycles
Maximum operating rate	3600 cyc/h 60 °C
Minimum switching current	5 mA for control circuit
Minimum switching voltage	17 V for control circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contacts 1.5 ms on energisation between NC and NO contacts
Insulation resistance	> 10 MOhm for control circuit
Height	127 mm
Width	85 mm
Depth	125 mm
Net weight	1.44 kg

Environment

Standards	CSA C22.2 No 14 EN 60947-5-1 EN 60947-4-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	UL BV LROS (Lloyds register of shipping) DNV CCC GL RINA CSA GOST
IP degree of protection	IP2x conforming to IEC 60529 IP2x conforming to VDE 0106
Protective treatment	TH (pollution degree 3) conforming to IEC 60068
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at U _c
Operating altitude	3000 m without
Fire resistance	850 °C conforming to IEC 60695-2-1
Shock resistance	10 gn contactor closed 8 gn contactor opened
Vibration resistance	2 gn 5...300 Hz contactor opened 4 gn 5...300 Hz contactor closed
Heat dissipation	4...5 W at 50/60 Hz for control circuit

Contractual warranty

Warranty	18 months
----------	-----------
