

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



Principal

Tip produs sau componenta	Starter de motor
Compatibilitate gama	Altivar 61Q Altivar 71Q Altivar 212 Altivar 71 Altivar&Nbsp;Process ATV600 Altivar&Nbsp;Process ATV900 Altivar 61
Aplicatie specifica produsului	Filtru de iesire
[In] calibru	215 A

ATV61HD11N4
 ATV61HD15N4
 ATV61HD18N4
 ATV61HU22S6X
 ATV61HU30S6X
 ATV61HU40S6X
 ATV61HU55N4
 ATV61HU55S6X
 ATV61HU75N4
 ATV61HU75S6X
 ATV61WD11N4
 ATV61WD11N4C
 ATV61WD15N4
 ATV61WD15N4C
 ATV61WD18N4
 ATV61WD18N4C
 ATV61WU55N4
 ATV61WU55N4C
 ATV61WU75N4
 ATV61WU75N4C
 ATV71HD11N4
 ATV71HD11Y
 ATV71HD15N4
 ATV71HD18N4
 ATV71HU15S6X
 ATV71HU22S6X
 ATV71HU30S6X
 ATV71HU40S6X
 ATV71HU55N4
 ATV71HU55S6X
 ATV71HU75N4
 ATV71HU75S6X
 ATV71PD11N4Z
 ATV71PU55N4Z
 ATV71PU75N4Z
 ATV71WD11N4
 ATV71WD15N4
 ATV71WD18N4
 ATV71WU55N4
 ATV71WU75N4
 ATV212HU15N4
 ATV61HD15Y
 ATV61HD18Y
 ATV61HD22N4
 ATV61HD22Y
 ATV61HD30N4
 ATV61HD30Y
 ATV61HD37N4
 ATV61WD22N4
 ATV61WD22N4C
 ATV61WD30N4
 ATV61WD30N4C
 ATV61WD37N4
 ATV61WD37N4C
 ATV71HD15Y
 ATV71HD18Y
 ATV71HD22N4
 ATV71HD22Y
 ATV71HD30Y
 ATV71HD37N4
 ATV71WD30N4
 ATV71WD37N4
 ATV630 variable speed drive - 2,2 kW, 500...690 V
 trifazic
 ATV630 variable speed drive - 3 kW, 500...690 V
 trifazic
 ATV630 variable speed drive - 4 kW, 500...690 V
 trifazic
 ATV630 variable speed drive - 5,5 kW, 500...690 V
 trifazic
 ATV630 variable speed drive - 7,5 kW, 500...690 V
 trifazic
 ATV630 variable speed drive - 11 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 2,2 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 3 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 4 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 5,5 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 7,5 kW, 500...690 V
 trifazic
 ATV930 variable speed drive - 11 kW, 500...690 V
 trifazic

Cantitate Incorporata	3
Conexiune electrica	Etichetă conector M10

Suplimentar

Lungimea maxima a cablului motorului	150 M cablu ecranat P motor 30...45 kW la 200...240 V 1 300 M cablu neecranat P motor 30...45 kW la 200...240 V 1 200 M cablu ecranat P motor 5,5...18,5 kW la 380...480 V 1 300 M cablu neecranat P motor 5,5...18,5 kW la 380...480 V 1 150 M cablu ecranat P motor 22...30 kW la 380...480 V 1 300 M cablu neecranat P motor 22...30 kW la 380...480 V 1 150 M cablu ecranat P motor 45...75 kW la 380...480 V 1 300 M cablu neecranat P motor 45...75 kW la 380...480 V 1 150 M cablu ecranat P motor 2,2...7,5 kW la 500...600 V 1 250 M cablu neecranat P motor 2,2...7,5 kW la 500...600 V 1 250 M cablu ecranat P motor 2,2...7,5 kW la 500...600 V 2 400 M cablu neecranat P motor 2,2...7,5 kW la 500...600 V 2 100 M cablu ecranat P motor 2,2...30 kW la 500...690 V 2 150 M cablu neecranat P motor 2,2...30 kW la 500...690 V 2 150 M cablu ecranat P motor 11...30 kW la 500...690 V 2 250 M cablu neecranat P motor 11...30 kW la 500...690 V 2 150 M cablu ecranat P motor 30...160 kW la 500...690 V 1 250 M cablu neecranat P motor 30...160 kW la 500...690 V 1 250 M cablu ecranat P motor 30...160 kW la 500...690 V 2 300 M cablu neecranat P motor 30...90 kW la 500...690 V 2 400 M cablu neecranat P motor 90...160 kW la 500...690 V 2 200 M cablu ecranat P motor 37 kW la 380...480 V 1 300 M cablu neecranat P motor 37 kW la 380...480 V 1 200 M cablu ecranat P motor 90 kW la 380...480 V 1 300 m cablu neecranat P motor 90 kW la 380...480 V 1
Dv/dt	500 V/μs maxim la 400 V 750 V/μs maxim la 500 V 1000 V/μs maxim la 690 V
Pierderi termice	430 W
Maximum drive output frequency	100 Hz
Temperatura ambientala de utilizare	-10...50 °C
Greutate neta	15,5 kg

Mediu

Grad de protectie IP	IP20 (cu kituri VW3A9612,613) IP00
Temperatura ambietala pentru depozitare	-25...70 °C

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	40,000 cm
Latime prima forma de impachetare	60,000 cm
Lungime prima forma de impachetare	40,000 cm
Greutate prima forma de impachetare	18,000 kg
Unitate de masura pentru a doua forma de impachetare	P06
Numar unitati in a doua forma de impachetare	2
Inaltime a doua forma de impachetare	75,000 cm
Latime a doua forma de impachetare	60,000 cm
Lungime a doua forma de impachetare	80,000 cm
Greutate a doua forma de impachetare	44,500 kg

Sustenabilitatea ofertei

Regulamentul REACH	Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conformitate proactivă (Produs în afara domeniului de aplicare a EU RoHS) Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	Declaratia RoHS China
Informatii privind scutirea de la RoHS	Da


Garanție contractuală

Garantie	18 months
----------	-----------


Dimensions

Front View

The choke comprise 3 components



Right View



Dimensions in mm

a	b	c	G	H	Ø
170	250	100	150	75	9 x 13

Dimensions in in.

a	b	c	G	H	Ø
6.69	9.84	3.94	5.91	2.95	0.35 x 0.51

Horizontal Mounting

