

Product data sheet

Characteristics

33661

MX shunt trip release, Compact NS 630b to Compact NS 3200, 100 VDC to 130 VDC, 100 VAC to 130 VAC 50/60 Hz



Main

Range	ComPacT
Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	ComPact NS630b...1600 ComPact NS1600b...3200
Voltage release type	Opening coil Instantaneous voltage release
Control type	Standard
[Uc] control circuit voltage	100...130 V AC 50/60 Hz 100...130 V DC
Circuit breaker mounting mode	Fixed

Complementary

Operating threshold	0.7...1.1 x Un opening
Response time	50 ms +/- 10 % for Compact NS630b...1600 50 ms +/- 10 % for Compact NS1600b...3200 55 ms +/- 10 % for MasterPact NT 70 ms +/- 10 % for MasterPact NW
Supply holding power	4.5 VA
Accessory / separate part category	Spare part for MasterPact NT Spare part for MasterPact NW Spare part for ComPacT NS630b...1600 new generation Spare part for ComPacT NS1600b...3200 new generation

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	150.0 g
Package 1 Height	3.5 cm
Package 1 width	6.3 cm
Package 1 Length	8.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.55 kg
Package 2 Height	9.0 cm
Package 2 width	13.2 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	19.12 kg
Package 3 Height	30.0 cm
Package 3 width	30.0 cm
Package 3 Length	40.0 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------