

Product data sheet

Characteristics

MGP0403X

Powerpact 4 - Molded Case Circuit Breaker -
3P - 40A - 415 V -



Main

Range of product	PowerPacT 4
Product or component type	Circuit breaker
Device application	Distribution
Poles description	3P
[In] rated current	40 A at 40 °C
[Ue] rated operational voltage	415 V AC 50/60 Hz
Suitability for isolation	Yes conforming to BS EN 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	36 kA Icu at 415 V AC 50/60 Hz
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
Control type	Toggle
Circuit breaker mounting mode	Panel-mounted

Complementary

[Ui] rated insulation voltage	800 V
[Uimp] rated impulse withstand voltage	8 kV
[Ics] rated service short-circuit breaking capacity	36 kA at 415 V AC 50/60 Hz
Mechanical durability	50000 cycles
Electrical durability	50000 Cycles at 440 V In/2 30000 cycles at 440 V In
Mounting support	Backplate
Mounting position	Horizontal and vertical
Number of modules	3 module(s)35 mm
Protection type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip unit rating	40 A at 40 °C
Thermal protection adjustment range	28...40 A
Earth-leakage protection	Without
Product destination	250 A panelboard 400/630 A panelboard

Environment

Standards	BS EN 60947-2
-----------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------