

Product data sheet

Characteristics

XS8G12MA230

inductive sensor XS8 12x40x26 - plastic -
Sn4mm - 24..240VAC/DC - cable 2m



Main

Range of product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS8
Sensor design	Form 12 x 40 x 26
Size	26 mm
Body type	Fixed
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	4 mm
Discrete output function	1 NO
Electrical connection	Cable
Cable length	2 m
Wire insulation material	PVC
[Us] rated supply voltage	24...210 V DC 24...240 V AC 50/60 Hz
Switching capacity in mA	5...200 mA
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Detection face	Lateral
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Front material	Plastic
Operating zone	0...3.2 mm
Differential travel	3...20% of Sr
Repeat accuracy	<= 10% of Sr
Output circuit type	AC/DC
Cable composition	2 x 0.34 mm ²
Status LED	Output state: 1 LED (yellow)
Supply voltage limits	20...264 V AC/DC
Maximum residual current	0.8 MA open state 24 V 1.5 mA open state 120 V
Switching frequency	<= 25 Hz AC <= 250 Hz DC
Maximum voltage drop	<5.5 V (closed)
Maximum delay first up	40 ms
Maximum delay response	1 ms
Maximum delay recovery	2 ms
Marking	CE

Depth	26 mm
Height	40 mm
Width	12 mm



Environment

Product certifications	UL[RETURN]CCC[RETURN]CSA
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.5 cm
Package 1 Length	14.0 cm
Package 1 Weight	93.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	28
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.985 kg
Unit Type of Package 3	P06
Number of Units in Package 3	448
Package 3 Height	75 cm
Package 3 Width	40 cm
Package 3 Length	80 cm
Package 3 Weight	66.664 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------