

## Product data sheet

### Characteristics

# MGU3.207.25

Unica - pushbutton switch - 10 A, 250 VAC - 2 m - ivory



### Main

Range	Unica
Device application	Control
Product or component type	Shutter control
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Fixing mode	Clip-in
Colour tint	Ivory

### Complementary

Device mounting	Flush
Number of modules	2 modules
Technology type	Electromechanical
Actuator	Rocker
Number of rocker	2
Switch function	1-pole 2-way
Switch application	Roller blind
Contacts type and composition	1 C/O
Mechanical interlocking	Interlock between up/down
[Iu] rated interrupted current	2.5 A for motor
Opening distance	> 3 mm
Marking	UP Down
Connections - terminals	Screwless terminals
Cable cross section	2.5 Mm <sup>2</sup> flexible cable 2.5 Mm <sup>2</sup> rigid cable
Minimum load breaking capacity	200 operations 1.25 I <sub>n</sub> and 1.1 U <sub>n</sub> , cos phi = 0.3
Electrical durability	40000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Standards	EN 60669-1 EMC directive LV directive
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Embedding depth	22 Mm
Depth	34 Mm
Width	45 Mm

Height	45 Mm
Net weight	0.0382 Kg

## Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	UV resistant Alcohol Acetone Window-cleaning fluid Petrol Liquid soap Bleach Oil

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 Cm
Package 1 Width	6.500 Cm
Package 1 Length	6.500 Cm
Package 1 Weight	38.500 G
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.500 Cm
Package 2 Width	13.500 Cm
Package 2 Length	33.000 Cm
Package 2 Weight	455.000 G
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15.000 Cm
Package 3 Width	30.000 Cm
Package 3 Length	40.000 Cm
Package 3 Weight	2.060 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------