

Tehničke karakteristike proizvoda Karakteristike

TM3DI16 modul TM3 - 16 ulaza



Osnovne informacije

Grupa proizvoda	Modicon TM3
Tip proizvoda ili komponente	Digitalni ulazni modul
Kompatibilnost grupe proizvoda	Modicon M241 Modicon M251 Modicon M221 Modicon M262
Broj digitalnih ulaza	16 za ulaz u skladu sa IEC 61131-2 tip 3
Logika digitalnog ulaza	Sink ili source (pozitivna/negativna)
Napon digitalnog ulaza	24 V
Struja digitalnog ulaza	7 mA za ulaz

Dopunske informacije

Broj digitalnih i/o	16
Potrošnja struje	40 mA pri 5 V DC putem bus konektora (u stanju ON) 5 mA pri 5 V DC putem bus konektora (u stanju OFF) 0 mA pri 24 V DC putem bus konektora (u stanju ON) 0 mA pri 24 V DC putem bus konektora (u stanju OFF)
Tip napona digitalnog ulaza	DC
Naponsko stanje 1 garantovano	15...28.8 V za ulaz
Garantovano stanje 1	≥ 2.5 mA (ulaz)
Naponsko stanje 0 garantovano	0...5 V za ulaz
Garantovano stanje 0	≤ 1 mA (ulaz)
Impedansa ulaza	3.4 k Ω
Vreme odziva	4 ms (uključenje) 4 ms (isključenje)
Lokalna signalizacija	Zastatus ulaza: 1 LED po kanalu (zelena)
Električna veza	10 x 1.5 mm ² odvojivi vijčani priključni blok sa razmak 3.81 mm podešavanje za ulaze
Maksimalna dužina kabla između dva uređaja	Neoklopljen kabl: <50 m za regularni ulaz
Izolacija	Između ulaza i interne elektronike pri 500 V AC Neizolovano između ulaza
Označavanje	CE
Držač za montažu	Tip TH35-15 šina u skladu sa IEC 60715 Tip TH35-7.5 šina u skladu sa IEC 60715 Ploča ili panel sa setom za montažu
Visina	90 mm
Dubina	84,6 mm
Širina	27,4 mm
Masa proizvoda	0,1 kg

Okruženje

Standardi	IEC 61131-2
Sertifikacija proizvoda	CE[RETURN]cULus[RETURN]UKCA[RETURN]RCM[RETURN]EAC[RETURN]cULus HazLoc
Otpornost na elektrostatičko pražnjenje	8 kV u vazduhu u skladu sa IEC 61000-4-2 4 kV na kontaktu u skladu sa IEC 61000-4-2
Otpornost na elektromagnetna polja	10 V/M 80 MHz...1 GHz u skladu sa IEC 61000-4-3 3 V/M 1.4 GHz...2 GHz u skladu sa IEC 61000-4-3 1 V/m 2 GHz...3 GHz u skladu sa IEC 61000-4-3
Otpornost na magnetna polja	30 A/m 50/60 Hz u skladu sa IEC 61000-4-8
Otpornost na brze prelaze	1 kV za I/O u skladu sa IEC 61000-4-4
Podnosivi naponski udar	1 kV I/O asimetrični režim u skladu sa IEC 61000-4-5 DC
Otpornost na emisije vezane sa vodovima, indukovane em poljima	10 V 0.15...80 MHz u skladu sa IEC 61000-4-6 3 V frekvencija uzorka (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) u skladu sa pomorska specifikacija (LR, ABS, DNV, GL)
Elektromagnetna emisija	Emisije vezane sa zračenjem - test nivo: 40 dBμV/m QP klasa A 10 m) pri 30... 230 MHz u skladu sa IEC 55011 Emisije vezane sa zračenjem - test nivo: 47 dBμV/m QP klasa A 10 m) pri 230... 1000 MHz u skladu sa IEC 55011
Temperatura okoline za rad	-10...35 °C vertikalne instalacije -10...55 °C horizontalnu instalaciju
Temperatura okoline za skladištenje	-25...70 °C
Relativna vlažnost	10...95 %, bez kondenzacije (u radu) 10...95 %, bez kondenzacije (skladištenje)
Ip stepen zaštite	IP20 sa zaštitnim poklopcem na mestu
Stepen zaprljanosti	2
Nadmorska visina za rad	EcoStruxure EV Charging Expert
Nadmorska visina skladištenja	0...3000 m
Otpornost na vibracije	3.5 mm pri 5...8,4 Hz na DIN šina 3 gn pri 8,4...150 Hz na DIN šina 3.5 mm pri 5...8,4 Hz na panel 3 gn pri 8,4...150 Hz na panel
Otpornost na udare	15 gn za 11 milisekundi


Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,345 cm
Package 1 Width	10,498 cm
Package 1 Length	12,471 cm
Package 1 Weight	210,8 g
Unit Type of Package 2	S04
Number of Units in Package 2	42
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10,5 kg
Unit Type of Package 3	P12
Number of Units in Package 3	504
Package 3 Height	105 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	132 kg

Održivost ponude


Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da

Dimensions




(*) 8.5 mm/0.33 in. when the clamp is pulled out.


Spacing Requirements




Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface




(1) Install a mounting strip

Mounting Hole Layout



Digital Input Module (16-channel, 24 Vdc)

Wiring Diagrams



The 4 COM terminals are connected internally

- (A) Sink wiring (positive logic)
- (B) Source wiring (negative logic)