

# LE4D12B7

TeSys LE - enclosed DOL starter - 12 A - 24 V  
AC coil



## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor Fuse disconnecter
[Ie] rated operational current	12 A AC-3
Motor power kW	3 kW at 220/230 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz 5.5 kW at 380/400 V AC 50/60 Hz 5.5 kW at 415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	12 A
Associated fuse rating	16 A 10 x 38 mm aM
Control type	Push-button start green I Push-button stop/reset red O

## Complementary

Cable entry number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	330 mm
Depth	175.5 mm
Net weight	1.96 kg

## Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------