

XVUC21B

Bottendel, Harmony XVU, med lock för översta enheten, svart, Ø60 mm, 24 V AC/DC



Produktdata

Produktområde	Harmony XVU
Typ av produkt eller komponent	Modulär ljuspelare
Typ av ljuspelare	Basenhet
Montagediameter	60 mm
Komponentnamn	XVU
Färg kåpa	Svart

Teknisk data

Kit består av	Basenhet Täcklock
Montering	Direkt eller rör montage
Material	PBT (polybutylen tereftalat) V-0 flamskyddad överensstämmer med UL 94 ABS (akrylnitrilbutadienstyren) V-0 flamskyddad överensstämmer med UL 94 PC (polykarbonat) V-0 flamskyddad överensstämmer med UL 94
Monterings sätt	Kundanpassning, upp till 5 enheter
[Us] driftspänning	24 V AC/DC - 15...10 %
Strömförbrukning	<= 400 mA
Längd	77 mm
Produktens vikt	0,11 kg

Miljö

Produktcertifieringar	CE[RETURN]UL[RETURN]CSA
Omgivande lufttemperatur för lagring	-40...70 °C
Omgivningstemperatur vid drift	-25...50 °C
Vibrationsbeständighet	2 gn
IP-kapslingsklass	IP65

Förpackningsinformation

Förpackningstyp 1	PCE
Antal i Förpackning 1	1
Förpackning 1 höjd	9,1 cm
Förpackning 1 bredd	26,8 cm
Förpackning 1 djup	9,0 cm
Förpackning 1 vikt	284,0 g
Förpackningstyp 2	S04
Antal i Förpackning 2	24
Förpackning 2 höjd	30,0 cm
Förpackning 2 bredd	40,0 cm
Förpackning 2 djup	60,0 cm
Förpackning 2 vikt	27,3 kg
Förpackningstyp 3	PAL


Number of Units in Package 3	96
Förpackning 3 höjd	60,0 cm
Förpackning 3 bredd	80,0 cm
Förpackning 3 djup	70,0 cm
Förpackning 3 vikt	31,04 kg

Hållbarhetsinformation


Hållbarhetsstatus	Green Premium-produkt
REACH-förordning	 REACH-Deklaration
EU RoHS-direktiv	Proaktiv överensstämmelse (produkten utanför EU RoHS juridiska omfattning)
Kviksilverfri	Ja
RoHS-förordning Kina	 RoHS-deklaration Kina
RoHS-undantagsinformation	 Ja
Miljöupplysning	 Produktmiljöprofil
Cirkulationsprofil	 Information Om Livslängdsslut

Base Unit DC

Dimensions



Modular Tower Lights Mounting



Drawing	Part number	Part name
A1	-	Top cover
-	Top cover (Silver)	
A2	XVUC9S	Buzzer unit
XVUC9SQ	Buzzer unit (Silver)	
A3	XVUC23	Green LED unit
XVUC24	Red LED unit	
XVUC25	Orange LED unit	
XVUC26	Blue LED unit	
XVUC27	White LED unit	
XVUC28	Yellow LED unit	
A4	XVUC29	Multi-LED unit
A5	XVUC29P	Multi-LED unit, Pulse signal
A6	XVUC9V	Sound unit
A7	XVUC9VP	Sound unit, Pulse signal
A8	XVUC020	Extender
XVUC020Q	Extender (Silver)	
A9	XVUC21B	DC body

Drawing	Part number	Part name
XVUC21BQ	DC body (Silver)	
A10	XVUC21M	AC body NPN
XVUC21MP	AC body PNP	
XVUC21MQP	AC body PNP (Silver)	
A11	XVUZ06	Flexible option
A12	XVUZ01	Fixing Unit - Direct mounting (3 pins)
XVUZ01Q	Fixing Unit - Direct mounting (Silver,3 pins)	
XVUZ03	Fixing Unit - Direct mounting (2 pins)	
XVUZ04	Fixing Unit - Direct mounting (4 pins)	
A13	XVUZ02	Fixing Unit - Plate with Pole (100 mm)
XVUZ02Q	Fixing Unit - Plate with Pole (100 mm, Silver)	
XVUZ400	Fixing Unit - Plate with Pole (400 mm)	
XVUZ800	Fixing Unit - Plate with Pole (800 mm)	
A14	XVUZ05	Fixing Unit - Plate with adjustment pole (100-385 mm)
A15	XVUC43	Green LED unit, Flash
XVUC44	Red LED unit, Flash	
XVUC45	Orange LED unit, Flash	
XVUC46	Blue LED unit, Flash	
XVUC47	White LED unit, Flash	
XVUC48	Yellow LED unit, Flash	
A16	XVUZ100T	Fixing Unit - Metal bracket with pole (100 mm)
XVUZ250T	Fixing Unit - Metal bracket with pole(250 mm)	
XVUZ400T	Fixing Unit - Metal bracket with pole (400 mm)	
A17	XVUZ12	Fixing plate for use on vertical support - black

Figure 1 consists of three parts: (A), (5), and (6). Part (A) is a perspective view of the device showing its dimensions: a height of 10 mm for the 24V version and 8 mm for the 100...240V version, and a width of 0.394 inches. Part (5) is a wiring diagram for the 24V AC/DC version, showing terminals L1 through L5, a common terminal (COM), and a 24V AC source. Part (6) is a wiring diagram for the 100...240V AC version, showing terminals L1 through L5, a common terminal (COM), and a 100...240V AC source.

- (A) Fixing Unit
- (1) Dimensions of Wiring size
- (2) Push-in Wire Connectors
- (3) Fuse : 2A ,250V
- (4) Fuse : 0.5A ,125V
- (5) Modular Tower Lights 24V AC/DC
- (6) Modular Tower Lights 100...240V AC
- L1 to Illuminated LED Units
- L5 :