


Product data sheet

Characteristics

NU503644Z

Noua Unica, Priza 2P+E 16A fara obturatoare, cu suport fixare si gheare, bej



Principal

Gama	Noua Unica
Tip produs sau componenta	Priza
Prezentare dispozitiv	Mecanism cu cadru de fixare si placa centrala
Montare dispozitiv	Incastrat
Numar priza	1
Configuratie poli priza	2P + E
Standard priza	Schuko
Descriere priza standard	Impamantare
Curent nominal	16 A

Suplimentar

Aplicatie a dispozitivului	Sursa de alimentare
[Ue] tensiune nominala	250 V
Tip retea electrica	C.a.
Frecventa retea electrica	50/60 Hz
Numar module	2 module
Mod de fixare	Gheare lungi
Culoare	Bej (RAL 1013)
Conexiuni - borne	Borne cu surub
Sectiune cablu	0...4 Mm ² cabluri, 2 - rigiditate cablu: flexibil 0...4 mm ² - rigiditate cablu: rigid
Capacitatea de rupere la sarcina minima	100 operatii 1.25 In si 1.1 Un, cos phi = 0,6
Durabilitate electrica	10000 cic, cos phi = 0,8
Rezistenta de izolatie	> 5 MΩ la 500 V
Rigiditate dielectrica	2000 V
Material	PC (polycarbonat): capac mecanism Zamak: suport de fixare PC (polycarbonat) GF10 FR: carcasa
Finisare suprafata	Lucios
Cantitate per set	Set de 1 flow-pack
Standarde	IEC 60884-1 DIN VDE 0620-1
Certificari produs	VDE
Adancime de montaj	30,5 mm
Adancime	40 mm
Latime	74,5 mm
Inaltime	74,5 mm
Greutate neta	0,0739 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Tratament suprafata	Netratat
Rezistenta la agenti chimici	Rezistent la alcool (70%) Rezistent la alcool (96%) Rezistent la acid A-lactic Rezistent la amoni cuaternar diluat Rezistent la inalbitor diluat Rezistent la amoniac diluat Rezistent la apa cu sapun Rezistent la detergent de cristal Rezistent la peroxid de hidrogen 10 volume Rezistent la hexan

Mediu

Temperatura ambientala de functionare	-5...35 °C
Temperatura ambietala pentru depozitare	-5...50 °C
Grad de protectie IK	IK01
Grad de protectie IP	IP20
Caracteristica de mediu	Rezistent UV Ulei Fluid de curatare a geamurilor Decolorant Alcool Benzina Acetona Sapun lichid

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	4,5 cm
Latime prima forma de impachetare	7,5 cm
Lungime prima forma de impachetare	7,5 cm
Greutate prima forma de impachetare	81,0 g
Unitate de masura pentru a doua forma de impachetare	BB1
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	8,0 cm
Latime a doua forma de impachetare	20,0 cm
Lungime a doua forma de impachetare	22,5 cm
Greutate a doua forma de impachetare	923,0 g
Unitate de masura pentru a treia forma de impachetare	S04
Numar unitati in a treia forma de impachetare	120
Inaltime a treia forma de impachetare	30,0 cm
Latime a treia forma de impachetare	40,0 cm
Lungime a treia forma de impachetare	60,0 cm
Greutate a treia forma de impachetare	11,731 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform  Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Raport de mediu	 Profilul Ambiental Al Produsului

Profil circularitate	Nu sunt necesare operatii de reciclare speciale
Minimum percentage of recycled plastic content	57

Garantie contractuală

Garantie	18 luni
----------	---------