

## Product data sheet

### Characteristics

## XVUC9VP

Semnal impuls Ø 60 mm, Unitate sunet XVU, IP54, 24 VDC, negru



### Principal

|                                            |                     |
|--------------------------------------------|---------------------|
| Gama de produse                            | Harmony XVU         |
| Tip produs sau componenta                  | Modular tower light |
| Unitate tip far sau baterie de indicatoare | Sound unit          |
| Diametrul de montaj                        | 60 mm               |
| Nume componenta                            | XVU                 |
| Culoare carcasa                            | Negru               |

### Suplimentar

|                                      |                                               |
|--------------------------------------|-----------------------------------------------|
| Tip semnalizare                      | Stabil                                        |
| Material                             | PBT + ABS (UL94-V0) V-2 conformitate cu UL 94 |
| Stil de asamblare                    | Ansamblu client                               |
| [Us] tensiune nominala de alimentare | 24 V c.c.                                     |
| Puterea disipata maxima in W         | 4,1 W                                         |
| Consum de curent                     | <= 190 mA                                     |
| Lungime                              | 155 mm                                        |
| Greutate neta                        | 0,219 kg                                      |

### Mediu

|                                         |                         |
|-----------------------------------------|-------------------------|
| Certificari produs                      | UE[RETURN]CSA[RETURN]UL |
| Temperatura ambietala pentru depozitare | -40...70 °C             |
| Temperatura ambientală de functionare   | -20...50 °C             |
| Grad de protectie IP                    | IP54                    |

### Unitati de ambalare

|                                                      |           |
|------------------------------------------------------|-----------|
| Unitate de masura pentru prima forma de impachetare  | PCE       |
| Numar unitati in prima forma de impachetare          | 1         |
| Inaltime prima forma de impachetare                  | 9,0 cm    |
| Latime prima forma de impachetare                    | 9,3 cm    |
| Lungime prima forma de impachetare                   | 26,7 cm   |
| Greutate prima forma de impachetare                  | 385,0 g   |
| Unitate de masura pentru a doua forma de impachetare | S04       |
| Numar unitati in a doua forma de impachetare         | 24        |
| Inaltime a doua forma de impachetare                 | 30,0 cm   |
| Latime a doua forma de impachetare                   | 40,0 cm   |
| Lungime a doua forma de impachetare                  | 60,0 cm   |
| Greutate a doua forma de impachetare                 | 10,425 kg |

|                                                       |           |
|-------------------------------------------------------|-----------|
| Unitate de masura pentru a treia forma de impachetare | P06       |
| Numar unitati in a treia forma de impachetare         | 96        |
| Inaltime a treia forma de impachetare                 | 80,0 cm   |
| Latime a treia forma de impachetare                   | 80,0 cm   |
| Lungime a treia forma de impachetare                  | 60,0 cm   |
| Greutate a treia forma de impachetare                 | 50,468 kg |


### Sustenabilitatea ofertei

|                                        |                                                                                                                                                 |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Stare ofertă sustenabilă               | Produs Green Premium                                                                                                                            |
| Regulamentul REACH                     | <a href="#"> Declaratia REACH</a>                              |
| Directiva RoHS UE                      | Conformitate proactivă (Produs în afara domeniului de aplicare a EU RoHS)                                                                       |
| Fara mercur                            | Da                                                                                                                                              |
| Regulamentul RoHS China                | <a href="#"> Declaratia RoHS China</a>                         |
| Informatii privind scutirea de la RoHS | <a href="#"> Da</a>                                            |
| Raport de mediu                        | <a href="#"> Profilul Ambiental Al Produsului</a>              |
| Profil circularitate                   | <a href="#"> Informatii Privind Sfarsitul Duratei De Viata</a> |

### Garanție contractuală

|          |         |
|----------|---------|
| Garantie | 18 luni |
|----------|---------|

## Dimensions




## Modular Tower Lights Mounting



| Drawing  | Part number          | Part name                    |
|----------|----------------------|------------------------------|
| A1       | -                    | Top cover                    |
| -        | Top cover (Silver)   |                              |
| A2       | XVUC9S               | Buzzer unit                  |
| XVUC9SQ  | Buzzer unit (Silver) |                              |
| A3       | XVUC23               | Green LED unit               |
| XVUC24   | Red LED unit         |                              |
| XVUC25   | Orange LED unit      |                              |
| XVUC26   | Blue LED unit        |                              |
| XVUC27   | White LED unit       |                              |
| XVUC28   | Yellow LED unit      |                              |
| A4       | XVUC29               | Multi-LED unit               |
| A5       | XVUC29P              | Multi-LED unit, Pulse signal |
| A6       | XVUC9V               | Sound unit                   |
| A7       | XVUC9VP              | Sound unit, Pulse signal     |
| A8       | XVUC020              | Extender                     |
| XVUC020Q | Extender (Silver)    |                              |
| A9       | XVUC21B              | DC body                      |

| Drawing   | Part number                                    | Part name                                             |
|-----------|------------------------------------------------|-------------------------------------------------------|
| XVUC21BQ  | DC body (Silver)                               |                                                       |
| A10       | XVUC21M                                        | AC body NPN                                           |
| XVUC21MP  | AC body PNP                                    |                                                       |
| XVUC21MQP | AC body PNP (Silver)                           |                                                       |
| A11       | XVUZ06                                         | Flexible option                                       |
| A12       | XVUZ01                                         | Fixing Unit - Direct mounting (3 pins)                |
| XVUZ01Q   | Fixing Unit - Direct mounting (Silver,3 pins)  |                                                       |
| XVUZ03    | Fixing Unit - Direct mounting (2 pins)         |                                                       |
| XVUZ04    | Fixing Unit - Direct mounting (4 pins)         |                                                       |
| A13       | XVUZ02                                         | Fixing Unit - Plate with Pole (100 mm)                |
| XVUZ02Q   | Fixing Unit - Plate with Pole (100 mm, Silver) |                                                       |
| XVUZ400   | Fixing Unit - Plate with Pole (400 mm)         |                                                       |
| XVUZ800   | Fixing Unit - Plate with Pole (800 mm)         |                                                       |
| A14       | XVUZ05                                         | Fixing Unit - Plate with adjustment pole (100-385 mm) |
| A15       | XVUC43                                         | Green LED unit, Flash                                 |
| XVUC44    | Red LED unit, Flash                            |                                                       |
| XVUC45    | Orange LED unit, Flash                         |                                                       |
| XVUC46    | Blue LED unit, Flash                           |                                                       |
| XVUC47    | White LED unit, Flash                          |                                                       |
| XVUC48    | Yellow LED unit, Flash                         |                                                       |
| A16       | XVUZ100T                                       | Fixing Unit - Metal bracket with pole (100 mm)        |
| XVUZ250T  | Fixing Unit - Metal bracket with pole(250 mm)  |                                                       |
| XVUZ400T  | Fixing Unit - Metal bracket with pole (400 mm) |                                                       |
| A17       | XVUZ12                                         | Fixing plate for use on vertical support - black      |

## Illuminated Units, Multi-LED and Audible Units Wiring



- (A) Fixing Unit  
 (1) Dimensions of Wiring size  
 (2) Push-in Wire Connectors  
 (3) Fuse : 0.5A , 125V  
 (4) Modular Tower Lights 24 VDC  
 (5) 5: Power supply, 24VDC (PNP application) or GND (NPN application)  
 (6) C: Power supply, 24VDC (NPN application) or GND (PNP application)  
 L1 to Illuminated LED Units  
 L4 :