



Main

Range	TeSys
Accessory / separate part category	Protection accessory
Product or component type	Current limiting module
Function of module	Increasing the breaking capacity of a circuit breaker
Range compatibility	TeSys GV2
Product compatibility	GV2RT GV2ME GV2P GV2L
Mounting location	35 mm DIN rail
[Ie] rated operational current	32 A
[Ith] conventional free air thermal current	63 A conforming to IEC 60947-1
Operating threshold	1000 A
Breaking capacity	<= 100 kA depending on protective device
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-1

Complementary

Connections - terminals	Screw clamp terminals 1 x 1.5...25 mm ² rigid Screw clamp terminals 2 x 1.5...10 mm ² rigid Screw clamp terminals 1 x 1.5...25 mm ² flexible without cable end Screw clamp terminals 2 x 1.5...10 mm ² flexible without cable end Screw clamp terminals 1 x 1.5...16 mm ² flexible with cable end Screw clamp terminals 2 x 1.5...4 mm ² flexible with cable end
Tightening torque	2.2 N.m
Net weight	0.32 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.