

Product data sheet

Characteristics

LC1G4004EHEN

High power contactor, TeSys Giga, 4 pole (4NO), AC-1 ≤ 440 V 550 A, standard version, 48...130 V wide band AC/DC coil



Main

Range	TeSys
Range of product	TeSys Giga
Product or component type	Contactor
Device short name	LC1G
Contactor application	Power switching
Utilisation category	AC-3 AC-3e AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	≤ 1000 V AC 50/60 Hz ≤ 460 V DC
[Ie] rated operational current	400 A (at ≤ 60 °C) at ≤ 440 V AC-3 550 A (at ≤ 40 °C) at ≤ 1000 V AC-1
[Uc] control circuit voltage	48...130 V AC 50/60 Hz 48...130 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at ≤ 60 °C) Drop-out: 0.1 Uc Max...0.45 Uc Min (at ≤ 60 °C)

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	550 A (at 40 °C)
Rated breaking capacity	3480 A at 440 V
[Icw] rated short-time withstand current	3.6 kA - 10 s 2.4 kA - 30 s 1.7 kA - 1 min 1.2 kA - 3 min 1.0 kA - 10 min
Associated fuse rating	500 A aM at ≤ 440 V for motor 315 A aM at ≤ 690 V for motor 630 A gG at ≤ 690 V
Average impedance	0.0001 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	30 W AC-1 - Ith 550 A 16 W AC-3 - Ith 400 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Irms rated making capacity	5090 A at 440 V
Coil technology	Built-in bidirectional peak limiting

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mechanical durability	8 Mcycles
Inrush power in VA (50/60 Hz, AC)	965 VA
Inrush power in W (DC)	760 W
Hold-in power consumption in VA (50/60 Hz, AC)	17.6 VA
Hold-in power consumption in W (DC)	7.8 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 cyc/h AC-1
Connections - terminals	Power circuit: bar 2 - busbar cross section: 32 x 10 mm Power circuit: lugs-ring terminals 1 185 mm ² Control circuit: push-in 1 0.2...2.5 mm ² - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.25...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: push-in 2 0.5...1.0 mm ² with cable end Control circuit: push-in 0.75...2.5 mm ² - cable stiffness: solid stranded without cable end Control circuit: push-in 0.75...2.5 mm ² - cable stiffness: flexible with cable end
Connection pitch	45 mm
Mounting support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1
Product certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	35 N.m
Height	225 mm
Width	185 mm
Depth	226 mm
Net weight	8.2 kg

Environment

IP degree of protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-60...80 °C
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Colour	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40...70 °C at U _c

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.0 cm
Package 1 Width	31.0 cm
Package 1 Length	31.0 cm
Package 1 Weight	9.386 kg
Unit Type of Package 2	S06
Number of Units in Package 2	4
Package 2 Height	75 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	47.544 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 개월
----------	-------



