

Product data sheet

Characteristics

XVBC2M4

unitate iluminata, lumina constanta, rosu, 230 V c.a.



Principal

Gama de produse	Harmony XVB Universal
Tip produs sau componenta	Baterie de indicatoare
Unitate tip far sau baterie de indicatoare	Unitate iluminata
Tip semnalizare	Stabil
Diametrul de montaj	70 mm
Nume componenta	XVBC
Material	Policarbonat
Sursa de lumina	LED integral, rosu
Tip bec	LED protejat
[Us] tensiune de alimentare nominala	230 V c.a.

Suplimentar

Stil de asamblare	Ansamblu client, pana la 5 unitati
Conexiuni - borne	Borne cu surub, <= 1 x 1,5 mm ² cu pini
[Ui] tensiune nominala de izolatie	250 V conformitate cu IEC 60947-1
Limita de tensiune nominala	0,85...1,1 Un conformitate cu SR EN 60947-5-1
Consum de curent	< 17 mA c.a.
[Uimp] tensiune de tinere la impuls	4 kV conformitate cu IEC 60947-1
CAD latime globala	70 mm
CAD inaltime globala	63 mm
CAD adancime globala	70 mm
Greutate neta	0,15 kg

Mediu

Grad de poluare	2
Certificari produs	CCC[RETURN]EAC[RETURN]CSA C22-2 Nr. 14[RETURN]UL 508
Standarde	SR EN 60947-5-1
Tratament protector	TC
Temperatura ambietala pentru depozitare	-40...70 °C
Clasa de protectie la electrocutare	Clasa I pe tubul suport conformitate cu IEC 61140 Clasa II pe bază conformitate cu IEC 61140
Grad de protectie IP	IP65 pe baza XVBZ0. conformitate cu SR EN 60529 IP66 pe bază conformitate cu SR EN 60529
Grad de protectie NEMA	Type 4X conformitate cu UL (în interior)

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	8,000 cm
Latime prima forma de impachetare	8,100 cm
Lungime prima forma de impachetare	9,200 cm
Greutate prima forma de impachetare	140,000 g
Unitate de masura pentru a doua forma de impachetare	S03
Numar unitati in a doua forma de impachetare	36
Inaltime a doua forma de impachetare	30,000 cm
Latime a doua forma de impachetare	30,000 cm
Lungime a doua forma de impachetare	40,000 cm
Greutate a doua forma de impachetare	5,705 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Directiva RoHS UE	Conformitate proactivă (Produs în afara domeniului de aplicare a EU RoHS)
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Raport de mediu	 Profilul Ambiental Al Produsului
Profil circularitate	Nu sunt necesare operatii de reciclare speciale
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.


Garantie contractuala

Garantie	18 luni
----------	---------

Indicator Bank without “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit XVBC21, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) Cover (supplied with XVBC21 base unit)

Number of illuminated or audible signalling units (no “flash”)	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

Indicator Bank with “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) “Flash” unit, to be ordered separately

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06