

## Product data sheet

### Characteristics

# CR1F400N7

TeSys F magnetic latching contactor - 3P(3 NO) - 400 A - 415 V AC coil



### Main

Range	TeSys
Product name	TeSys F
Product or component type	Magnetic latching contactor
Device short name	CR1F
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	1000 V AC 25...200 Hz
[Ie] rated operational current	400 A (at <40 °C) at ≤ 440 V AC AC-3 500 A (at <40 °C) at ≤ 440 V AC AC-1 370 A (at <40 °C) at ≤ 440 V AC AC-4
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	415 V AC 50/60 Hz
Irms rated making capacity	4500 A
Rated breaking capacity	4000 A at 220...440 V 3500 A at 500 V 1200 A at 1000 V 3000 A at 660/690 V
[Icw] rated short-time withstand current	3600 A 40 °C - 1 s 3600 A 40 °C - 5 s 3600 A 40 °C - 10 s 2400 A 40 °C - 30 s 1700 A 40 °C - 1 min 1200 A 40 °C - 3 min 1000 A 40 °C - 10 min
Associated fuse rating	400 A aM at ≤ 440 V 500 A BS88 at ≤ 440 V 500 A gG at ≤ 440 V
Average impedance	0.28 mOhm - Ith 500 A 50 Hz
[Ui] rated insulation voltage	1000 V conforming to IEC 60158-1 1000 V conforming to IEC 60947-4 1000 V conforming to BS 775 1500 V conforming to VDE 0110 group C
Power dissipation per pole	45 W AC-3 70 W AC-1
Connections - terminals	Lugs-ring terminals 2 cable(s) 150 mm <sup>2</sup> Bars 2 cable(s) - busbar cross section: 30 x 5 mm
Tightening torque	35 N.m
Operating time	40...75 ms latching 50...100 ms unlatching
Mechanical durability	1 Mcycles
Maximum operating rate	120 cyc/h 40 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Complementary

Control circuit voltage limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
Average consumption	1450 VA AC 50/60 Hz latching 12 VA AC 50/60 Hz unlatching

## Environment

Protective treatment	TC
Ambient air temperature for operation	-15...70 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating
Height	206 mm
Width	213 mm
Depth	219 mm
Net weight	9.1 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25 cm
Package 1 Width	23.5 cm
Package 1 Length	30 cm
Package 1 Weight	9.28 kg

## Contractual warranty

Warranty	18 months
----------	-----------