

## Product data sheet

### Characteristics

# GS2AH140

External rotary handle, TeSys GS, red handle, front mounting, 2 positions I-O, NEMA 3R, for GS 30-400A UL



### Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2EU TeSys TeSys GS GS2GU TeSys TeSys GS GS2JU TeSys TeSys GS GS2MU TeSys TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

### Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	CSA UL
Net weight	0.24 kg

### Environment

NEMA degree of protection	NEMA 3R/12
---------------------------	------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	12.000 cm
Package 1 Length	16.000 cm
Package 1 Weight	247.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.150 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------