

Product data sheet

Characteristics

LADT0

TeSys D - time delay auxiliary contact block - 1
NO + 1 NC screw clamp terminals



Main

Range	TeSys TeSys Deca
Product name	TeSys Deca
Product or component type	Time delay auxiliary contact block
Range compatibility	TeSys Deca CAD[RETURN]TeSys Deca LC1D[RETURN]TeSys F LC1F[RETURN]TeSys F CR1F
Mounting location	Front
Pole contact composition	1 NO + 1 NC
Contacts operation	Time delay
Timer type	On delay
Time delay range	0.3...3 s
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ie] rated operational current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] conventional free air thermal current	10 A (at 60 °C)
Standards	UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5
Product certifications	IECEE CB Scheme[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]IEA

Complementary

Irms rated making capacity	140 A at <= 690 V AC conforming to IEC 60947-5-1 250 A at <= 690 V DC conforming to IEC 60947-5-1
Permissible short-time rating	100 A 60 °C 1 s 120 A 60 °C 500 ms 140 A 60 °C 100 ms
Protection type	GG fuse 10 A
Mechanical durability	5 Mcycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 Ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact
Insulation resistance	> 10 MOhm
Connections - terminals	Screw clamp terminals 1 cable(s) 1...2.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 1...2.5 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1...2.5 mm ² rigid Screw clamp terminals 2 cable(s) 1...2.5 mm ² rigid Screw clamp terminals

Tightening torque	1.7 N.M - with screwdriver flat Ø 6 mm 1.7 N.M - with screwdriver Philips No 2 1.7 N.m - with screwdriver pozidriv No 2
Height	48 mm
Width	44 mm
Depth	61 mm
Colour	Dark grey




Environment

Environmental characteristic	Normal environment
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for storage	-60...80 °C
Ambient air temperature for operation	-40...70 °C
Operating altitude	3000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.200 cm
Package 1 Width	6.500 cm
Package 1 Length	5.000 cm
Package 1 Weight	74.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	140
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.018 kg
Unit Type of Package 3	P06
Number of Units in Package 3	1120
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	101.340 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------