

Product data sheet

Characteristics

LAD703B

TeSys D thermal overload relays - remote electrical stop - 24 V DC/AC



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LR3D313...LR3D365 LR3D01...D35 LRD01...35 LR9G
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	4.9 cm
Package 1 Length	5.3 cm
Package 1 Weight	110.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.705 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------