

Tehničke karakteristike proizvoda

Karakteristike

XUB0APSNL2

fotoelektrični senzor - XUB - multi - Sn 0..20m -
12..24VDC - kabl 2m



Osnovne informacije

Grupa proizvoda	Telemecanique fotoelektrični senzori XU
Ime serije	Opšta upotreba multimodni
Tip elektronskog senzora	Fotoelektrični senzor
Ime senzora	XUB
Dizajn senzora	Cilindrični M18
Sistem detekcije	Multimodno
Materijal	Plastika
Linija detekcije	Duž ose kućišta
Tip izlaznog signala	Digitalni
Tip kola napajanja	DC
Tehnika ožičenja	3-žični
Tip digitalnog izlaza	PNP
Funkcija digitalnog izlaza	1 NO ili 1 NC podesivo
Električna veza	Kablom
Dužina kabla	2 m
Specifične primene proizvoda	-
Emisija	Infracrvena difuzno Infracrvena difuzno sa prigušenjem pozadine Infracrvena thru beam Crvena polarizovano refleksno
[sn] nazivna osetljivost	3 M polarizovano refleksno potreban reflektor XUZC50 20 M thru beam potreban predajnik XUB0AKSNL2T 0,12 M difuzno sa prigušenjem pozadine 0,3 m difuzno

Dopunske informacije

Materijal kućišta	PBT
Materijal sočiva	PMMA
Maksimalna udaljenost	0,12 M difuzno sa prigušenjem pozadine 0,4 M difuzno 30 M thru beam 4,5 m polarizovano refleksno
Priključak na vozilu	Tranzistorski
Dodatak na izlaz	Bez
Materijal izolacije žice	PvR
Statusne led lampice	1 LED (zelena) za napajanje 1 LED (crvena) za nestabilnost 1 LED (žuta) za izlazno stanje
[us] nazivni napon	12...24 V DC sa zaštitom od promene polariteta
Granice napona	10...36 V DC
Preklopna moć u ma	<= 100 mA (zaštita od preopterećenja i kratkog spoja)
Frekvencija preklapanja	<= 250 Hz
Maksimalni pad napona	<1,5 V (zatvoreno stanje)
Potrošnja struje	35 mA bez opterećenja

Maksimalno kašnjenje prvog uključanja	200 milisekundi
Maksimalno kašnjenje odgovora	2 milisekundi
Maksimalno kašnjenje oporavka	2 milisekundi
Podešavanje	Samoučenje
Prečnik	18 mm
Dužina	64 mm
Masa proizvoda	0,095 kg

Okruženje

Sertifikacija proizvoda	UL[RETURN]CE[RETURN]CSA
Temperatura okoline za rad uređaja	-25...55 °C
Temperatura okoline za skladištenje	-40...70 °C
Otpornost na vibracije	7 gn, amplituda = +/- 1.5 mm (f = 10...55 Hz) u skladu sa IEC 60068-2-6
Otpornost na udare	30 gn (trajanje = 11 milisekundi) u skladu sa IEC 60068-2-27
Ip stepen zaštite	IP65 dvostruka izolacija u skladu sa IEC 60529 IP67 dvostruka izolacija u skladu sa IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,2 cm
Package 1 Width	9,5 cm
Package 1 Length	13,2 cm
Package 1 Weight	99 g
Unit Type of Package 2	S02
Number of Units in Package 2	22
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2,684 kg


Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Informacije o RoHS izuzecima	 Da

Ugovorna garancija


Garancija	18 meseci
-----------	-----------

Dimensions



Connections and Schemes

PNP




BN : Brown

BU : Blue


BK : Black

Detection Curves

With Thru-beam Accessory (Thru-beam)



Without Accessory (Diffuse)




1 : White 90%

2 : Grey 18%

Object 10 x 10 cm

Without Accessory (Diffuse with background suppression)




1 : White 90%

2 : Grey 18%

Object 10 x 10 cm

With reflector (Polarised reflex)



With reflector XUZC50

Variation of Usable Sensing Distance S_u (Without accessory, with adjustable background suppression)

Teach Mode at Minimum



Teach Mode at Maximum



- (1) Black 6%
- (2) Grey 18%
- (3) White 90%
- (4) Sensing range
- (5) Non sensing zone (matt surfaces)

A-B : Object reflection coefficient

- (1) Black 6%
- (2) Grey 18%
- (3) White 90%
- (4) Sensing range
- (5) Non sensing zone (matt surfaces)

Variation of Usable Sensing Distance

Minimum Setting



Maximum Setting



- (1) Black 6%
- (2) Grey 18%
- (3) White 90%
- (4) Sensing range
- (5) Non sensing zone (matt surfaces)

A-B : Object reflection coefficient

- (1) Black 6%
- (2) Grey 18%
- (3) White 90%
- (4) Sensing range
- (5) Non sensing zone (matt surfaces)